



SIRIUS ACT ID key-operated switches

The right Starter Kit for your application

The electronic ID key-operated switches from the SIRIUS ACT family of commanding and signaling devices has proven its high flexibility compared to conventional solutions for many years. Unique key IDs are used to correctly assign authorizations. Take a look at the variety of ID key-operated switches available and see for yourself how our Starter Kits work.

Choice of preprogrammed and freely programmable options for the perfect application solution.

The two Starter Kits contain everything you need to get started easily:

- SIRIUS ACT components, ID key-operated switch incl. ID key
- Label holder with 4 labels
- Partially insulated SIRIUS screwdriver
- IO-Link electronic module (pre-programmed or freely programmable)

SIRIUS ACT ID key-operated switch Starter Kits:



Starter Kit 1

ID key-operated switch with pre-programmed IO-Link electronic module

Article No.: 3SU1900-0XD10-0AA0

IO-Link module with four preprogrammed authorization levels

Colored keys: Authorization levels encoded at the factory

White key:

- Authorization levels 1–4 freely programmable via IO-Link (individual special lock)
- Simple disabling if keys for special locks are lost
- Easy plant integration via TIA Portal (Port Configuration Tool)



Starter Kit 2

ID key-operated switch with freely programmable IO-Link electronic module

Article No.: 3SU1900-0XE10-0AA0

Fulfillment of customer-specific application requirements

IO-Link is used to transmit the following signals:

- Impulse rotate left
- Impulse rotate right
- ID key inserted
- ID number

The four LEDs on the actuating element can be encoded as required.

























Please note: To use the freely programmable IO-Link module*, an S7 program must be programmed in TIA Portal Step 7

*Prepared program blocks from different application examples for the use of the freely programmable electronic module can be found at:
<https://support.industry.siemens.com/cs/en/view/109780526>

Advantages of the two Starter Kits at a glance:

- Individual authorization management for groups or individuals
- Unambiguous identification of users
- Increased plant safety
- Degree of protection IP65
- Different colored RFID keys for each authorization level
- Unrestricted selection and combination of authorization levels, freely programmable for individual special locks via IO-Link
- Easy integration into plant via TIA Portal (Port Configuration Tool)
- Highly flexible authorization assignment

SIRIUS ACT ID key-operated switches complete portfolio - for greater security in your plant

		Accessories																		
 <p>Actuating element Plastic, black 3SU1000-4WS10-0AA0</p>  <p>Actuating element Plastic with front ring of metal, matte 3SU1030-4WS10-0AA0</p>	 <p>Holder Plastic 3SU1500-0AA10-0AA0</p>	 <p>Standard module (only green to blue keys can be used) 3SU1400-1GC10-1AA0 or IO-Link module With 5 preprogrammed electronic switches 3SU1400-1GD10-1AA0 or IO-Link module* With freely programmable electronic switches 3SU1400-1GE10-1AA0</p>	 <p>ID key</p> <table border="0"> <tr> <td></td> <td>1st authorization level</td> <td>3SU1900-0FV40-0AA0</td> </tr> <tr> <td></td> <td>2nd authorization level</td> <td>3SU1900-0FW30-0AA0</td> </tr> <tr> <td></td> <td>3rd authorization level</td> <td>3SU1900-0FX20-0AA0</td> </tr> <tr> <td></td> <td>4th authorization level</td> <td>3SU1900-0FY50-0AA0</td> </tr> <tr> <td></td> <td>5th authorization level</td> <td>3SU1900-0FU60-0AA0</td> </tr> </table>				1st authorization level	3SU1900-0FV40-0AA0		2nd authorization level	3SU1900-0FW30-0AA0		3rd authorization level	3SU1900-0FX20-0AA0		4th authorization level	3SU1900-0FY50-0AA0		5th authorization level	3SU1900-0FU60-0AA0
		1st authorization level	3SU1900-0FV40-0AA0																	
	2nd authorization level	3SU1900-0FW30-0AA0																		
	3rd authorization level	3SU1900-0FX20-0AA0																		
	4th authorization level	3SU1900-0FY50-0AA0																		
	5th authorization level	3SU1900-0FU60-0AA0																		
 <p>Dust cover for ID key-operated switch, transparent 3SU1900-0EM70-0AA0</p>	 <p>Enclosure for 4-position selector, coordinate, ID key-operated and sensor switches 3SU1801-1AA00-1AA1</p>	 <p>Flat label holder for 4 inscription plates, 17.5 x 27.5 mm Snap-on 3SU1900-0BT10-0AA0</p>	 <p>Self-adhesive 3SU1900-0BS10-0AA0</p>																	

*Prepared program blocks from different application examples for use with the freely programmable electronic module can be found at: <https://support.industry.siemens.com/cs/en/de/view/109780526>

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.

Published by
Siemens AG

Smart Infrastructure
Electrical Products
Werner-von-Siemens-Str. 48–50
92224 Amberg, Germany

For the U.S. published by
Siemens Industry Inc.

100 Technology Drive
Alpharetta, GA 30005
United States

Article No.: SIEP-B10021-00-7600
Dispo 27602 SB 06201.0
Printed in Germany
© 2020 Siemens