



NOTES:  
 1. FINISH: GRAY  
 2. CABINET: 16 GA GALV STEEL.  
 3. 100 AMP, 120/240 VAC, 1PHASE, 3 WIRE  
 4. SEALING RING, HUB COVER PLATE ASSEMBLY, & NEMA INSTRUCTION SHEET PLSCED IN APPROX. LOCATION SHOWN INSIDE OF BOX BEFORE PULL-SECTION COVER IS SECURED.  
 5. UL LISTED - E27485

CATALOG NO. MM0202L1100EY  
 TYPE 3R ENCLOSURE (RAINPROOF) TOP FEED ONLY.  
 SUITABLE FOR USE AS SERVICE EQUIPMENT WHEN NOT MORE THAN SIX MAIN DISCONNECTING MEANS ARE PROVIDED. WHEN USED AS SERVICE EQUIPMENT, BOND NEUTRAL AND APPLY \*SERVICE DISCONNECT\* LABEL NEAR THE DISCONNECT HANDLE.  
 DEVICE RATING: 100 AMPS MAXIMUM; 120/240 VAC (4 JAW METER); SINGLE PHASE, THREE WIRE: OR 208Y/120 VAC (5 JAW METER), SINGLE PHASE, THREE WIRE.  
 LIMITED TO TWO POLE BREAKERS.  
 METER SOCKET RATING: 100 AMPS CONTINUOUS.

THIS DEVICE HAS A MAXIMUM SHORT CIRCUIT RATING OF 65,000 RMS SYMMETRICAL AMPERES AT 240 VAC MAXIMUM. (WATTHOUR METER NOT INCLUDED IN THE SHORT CIRCUIT CURRENT RATING). THE ACTUAL RATING IS DEPENDENT ON THE BRANCH BREAKER INSTALLED IN THIS PANELBOARD AND THE REMOTE MAIN BREAKER OR FUSE DEVICE, IF ANY, INSTALLED AHEAD OF THIS PANELBOARD. THE CORRECT BRANCH BREAKERS AND MAIN SERIES COMBINATIONS TO BE USED WITH THE VARIOUS SHORT CIRCUIT CURRENT RATINGS ARE LISTED IN THE TABULATION BELOW. ANY CIRCUIT BREAKER INSTALLED OR REPLACED IN THIS PANELBOARD MUST BE MANUFACTURED BY SIEMENS AND MUST BE OF THE CORRECT TYPE AS INDICATED IN THE TABULATION BELOW

MAX short circuit current rating in RMS symmetrical Amperes	WHEN THE INSTALLED BREAKER TYPE IS:
65,000	Murray MP-MT or Siemens HQP
22,000	Murray MP-HT, MP-MT or Siemens QPH, HQP
10,000	MURRAY MP-T, MP-GT OR Siemens QP, QPF

\*FUSE or \*BREAKER RATING MUST BE GREATER THAN OR EQUAL TO THE DEVICE SHORT CIRCUIT CURRENT RATING.

TERMINAL RANGES - AWG AND TORQUE (LB-IN)  
 TERMINALS RATED AL/CU EXCEPT AS NOTED.  
 PHASE LINE: #2/0-6: TORQUE (110)  
 NEUTRAL LINE: #1/0-14:  
 TORQUE #1/0-3 (50), #4-6 (45), #6 (40), #10-14 (35)  
 NEUTRAL LOAD, SERVICE GROUND: #1/0-14CU, #1/0-12AL (LARGE TERMINALS):  
 TORQUE #1/0-6 (45), #8 (40), #10-14 (35)  
 EQUIPMENT GROUND: #6-14CU, #6-12AL (SMALL TERMINALS):  
 TORQUE #6 (35), #8 (25), #10-14 (20).  
 TEST BLOCK CONTACT NUT (5/8" ACROSS FLATS); TORQUE 50 LB-IN.

TERMINALS SUITABLE FOR USE WITH 60/75° C, AL/CU INSULATED WIRE.

FOR EQUIPMENT GROUND BAR ORDER ECLX SERIES, FOR 5TH JAW ORDER EC5J, IF HUB IS REQUIRED SELECT FROM LIST BELOW.  
 RX TYPE HUBS

SIZE	CAT. NO
1 1/4"	EC38597
1 1/2"	EC38598
2"	EC38599
2 1/2"	EC38600

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES		-CONFIDENTIAL-PROPERTY OF Siemens Energy & Automation, Inc. Residential Products Division			
TOLERANCES: .XX .XXX		SKT 100A 1P (2)HO EUSERC			
HOLE DIAMETER ANGULAR UNDIMENSIONED 90° ANGLES	DWN WRB CHK	DATE 5/8/07	SIZE B	ISSUE RELEASE NO.	DWG NO. MM0202L1100EY
	APVD	DATE	SCALE	DO NOT SCALE DRAWING	SHEET 1 OF 1

06-26-14 REV PER 2014-056. CJD