

Accreditation



The Deutsche Akkreditierungsstelle attests with this **Accreditation Certificate** that

Siemens Aktiengesellschaft

with its testing laboratory

**Siemens Aktiengesellschaft
Prüffeld der Schaltwerke - Mittelspannung
Nonnendammallee 104, 13629 Berlin**

meets the minimum requirements according to DIN EN ISO/IEC 17025:2018 for the conformity assessment activities listed in the annex to this certificate. This includes additional existing legal and normative requirements, including those in relevant sectoral schemes.

The management system requirements of DIN EN ISO/IEC 17025 are written in the language relevant to the operations of testing laboratories and confirm generally with the principles of DIN EN ISO 9001.

This accreditation was issued in accordance with Art. 5 Para. 1 Sentence 2 of Regulation (EC) 765/2008, after an accreditation procedure was carried out in compliance with the minimum requirements of DIN EN ISO/IEC 17011 and on the basis of a review and decision of the appointed accreditation committees.

This accreditation certificate only applies in connection with the notices of 31.03.2023 with accreditation number D-PL-11055-10.

It consists of this cover sheet, the reverse side of the cover sheet and the following annex with a total of 07 pages.

Registration number of the accreditation certificate: **D-PL-11055-10-00**

Berlin, 31.03.2023



Florian Burkart
Head of Technical Unit

Translation issued:
31.03.2023

Florian Burkart
Head of Technical Unit

The certificate together with the annex reflects the status as indicated by the date of issue. The current status of any given scope of accreditation can be found in the directory of accredited bodies maintained by Deutsche Akkreditierungsstelle GmbH (www.dakks.de).

This document is a translation. The definitive version is the original German accreditation certificate.

See notes overleaf

Deutsche Akkreditierungsstelle GmbH

Office Berlin
Spittelmarkt 10
10117 Berlin

Office Frankfurt am Main
Europa-Allee 52
60327 Frankfurt am Main

Office Braunschweig
Bundesallee 100
38116 Braunschweig

The Deutsche Akkreditierungsstelle GmbH (DAkKS) is the entrusted national accreditation body of the Federal Republic of Germany according to § 8 section 1 AkkStelleG in conjunction with § 1 section 1 AkkStelleGBV. DAkKS is designated as the national accreditation authority by Germany according to Art. 4 Para. 4 of Regulation (EC) 765/2008 and clause 4.7 of DIN EN ISO/IEC 17000.

Pursuant to Art. 11 section 2 of Regulation (EC) 765/2008, the accreditation certificate shall be recognised as equivalent by the national authorities within the scope of this Regulation as well as by the WTO member states that have committed themselves in bilateral or multilateral mutual agreements to recognise the certificates of accreditation bodies that are members of ILAC or IAF as equivalent.

DAkKS is a signatory to the multilateral agreements for mutual recognition of the European co-operation for Accreditation (EA), International Accreditation Forum (IAF) and International Laboratory Accreditation Co-operation (ILAC).

The up-to-date state of membership can be retrieved from the following websites:

EA: www.european-accreditation.org

ILAC: www.ilac.org

IAF: www.iaf.nu

Deutsche Akkreditierungsstelle

Annex to the Accreditation Certificate D-PL-11055-10-00 according to DIN EN ISO/IEC 17025:2018

Valid from: 31.03.2023

Date of issue: 31.03.2023

Holder of accreditation certificate:

Siemens Aktiengesellschaft

with its testing laboratory

**Siemens Aktiengesellschaft
Prüffeld der Schaltwerke - Mittelspannung
Nonnendammallee 104, 13629 Berlin**

The testing laboratory meets the minimal requirements of DIN EN ISO/IEC 17025:2018 and, if applicable, additional legal and normative requirements, including those in relevant sectoral schemes, in order to carry out the conformity assessment activities listed below.

The management system requirements of DIN EN ISO/IEC 17025 are written in the language relevant to the operations of testing laboratories and confirm generally with the principles of DIN EN ISO 9001.

Tests in the fields:

**High-Voltage Switch and Controlgear
Power Engineering Equipment**

The testing laboratory is permitted, without being required to inform and obtain prior approval from DAkkS, to use standards or equivalent testing methods listed here with different issue dates.

The testing laboratory maintains a current list of all testing methods within the flexible scope of accreditation.

This certificate annex is only valid together with the written accreditation certificate and reflects the status as indicated by the date of issue. The current status of any given scope of accreditation can be found in the directory of accredited bodies maintained by Deutsche Akkreditierungsstelle GmbH at <https://www.dakks.de>.

Abbreviations used: see last page

Page 1 of 7

This document is a translation. The definitive version is the original German annex to the accreditation certificate.

Testing field	Standard / In-House Procedure / Version	Title of Standard or In-House Procedure (Deviations / Modifications of Standard)	Test Range / Restrictions
Electrical engineering	IEC 62271-1:2017/ AMD:2021	High-voltage switchgear and controlgear - Part 1: Common specifications	
Electrical engineering	IEEE 4:2013	IEEE Standard Techniques for High-Voltage Testing	
Electrical engineering	IEEE Std C37.20.2:2015	IEEE Standard for Metal-Clad Switchgear	
Electrical engineering	IEEE Std C37.20.3:2013	IEEE Standard for Metal-Enclosed Interrupter Switchgear	
Electrical engineering	IEEE Std C37.100:1992	IEEE Standard Definitions for Power Switchgear	
Electrical engineering	IEEE Std C37.100.1:2018	Common requirements for high voltage power switchgear rated above 1000 V	
Electrical engineering	GOST 1516.3-96	Electrical equipment for a.c. voltages from 1 to 750 kV - Requirements for electric strength of insulation	
Circuit-breakers			
Electrical engineering	IEC 62271-100:2021	High-voltage switchgear and controlgear - Part 100: High-voltage alternating-current circuit- breakers	
Electrical engineering	IEC 62271-101:2021	High-voltage switchgear and controlgear - Part 101: Synthetic testing	
Electrical engineering	IEC 62271-110:2017	High-voltage switchgear and controlgear - Part 110: Inductive load switching	
Electrical engineering	IEC 62271-111:2019 IEEE Std C37.60:2019	High voltage switchgear and controlgear - Part 111: Overhead, pad-mounted, dry vault, and submersible automatic circuit reclosers and fault interrupters for alternating current systems up to 38 kV	

Annex to the Accreditation Certificate D-PL-11055-10-00

Testing field	Standard / In-House Procedure / Version	Title of Standard or In-House Procedure (Deviations / Modifications of Standard)	Test Range / Restrictions
Electrical engineering	DIN EN 50152-1:2013 VDE 0115-320-1:2013 EN 50152-1:2012	Railway applications - Fixed installations - Particular requirements for AC switchgear - Part 1: Single-phase circuit-breakers with Un above 1 kV	
Electrical engineering	DIN EN 50152-2:2013 VDE 0115-320-2:2013 EN 50152-2:2012	Railway applications - Fixed installations - Particular requirements for a.c. switchgear - Part 2: Single-phase disconnectors, earthing switches and switches with Un above 1 kV	
Electrical engineering	IEC 60077-1:2017	Railway applications - Electric equipment for rolling stock - Part 1: General service conditions and general rules	
Electrical engineering	IEC 60077-2:2017	Railway applications - Electric equipment for rolling stock - Part 2: Electrotechnical components - General rules	
Electrical engineering	IEC 60077-4:2019	Railway applications - Electric equipment for rolling stock - Part 4: Electrotechnical components; Rules for AC circuit-breakers	
Electrical engineering	IEEE Std C37.04:2018	IEEE Standard Rating Structure for AC High-Voltage Circuit Breakers	
Electrical engineering	IEEE C37.06:2009	AC High-Voltage Circuit Breakers Rated on a Symmetrical Current Basis - Preferred Ratings and Related Required Capabilities	
Electrical engineering	IEEE Std C37.09:2018	IEEE Standard Test Procedure for AC High-Voltage Circuit Breakers Rated on a Symmetrical Current Basis	
Electrical engineering	IEEE Std C37.011:2019	IEEE Application Guide for Transient Recovery Voltage for AC High-Voltage Circuit Breakers	
Electrical engineering	IEEE Std C37.012:2014	IEEE Application Guide for Capacitance Current Switching for AC High-Voltage Circuit Breakers	
Electrical engineering	IEC/IEEE 62271-37-013: 2021	High-voltage switchgear and controlgear – Part 37-013: Alternating current generator circuit-breakers	
Electrical engineering	IEEE Std C37.11:2014	IEEE Standard Requirements for Electrical Control for AC High-Voltage Circuit Breakers Rated on a Symmetrical Current Basis	-

Testing field	Standard / In-House Procedure / Version	Title of Standard or In-House Procedure (Deviations / Modifications of Standard)	Test Range / Restrictions
Electrical engineering	ANSI C37.54:2003	Conformance Test Procedures for Indoor Alternating Current High-Voltage Circuit Breakers Applied as Removable Elements in Metal-Enclosed Switchgear Assemblies	-
Electrical engineering	CSA C22.2 No. 31-18:2018	Switchgear assemblies	
Electrical engineering	GOST R 52565-2006	Alternating-Current Circuit-Breakers for Voltage from 3 to 750 kV	
Electrical engineering	IEC 62505-1: 2016	Railway applications - Fixed installations - Particular requirements for AC switchgear - Part 1: Circuit-breakers with Un above 1 kV	
Electrical engineering	IEC 62505-2: 2016	Railway applications - Fixed installations - Particular requirements for a.c. switchgear - Part 2: Disconnectors, earthing switches and switches with Un above 1 kV	
Switch			
Electrical engineering	IEC 62271-103:2021	High-voltage switchgear and controlgear - Part 103: Switches for rated voltages above 1 kV up to and including 52 kV	
Electrical engineering	IEC 62271-105:2021	High-voltage switchgear and controlgear - Part 105: Alternating current switch-fuse combinations	-
Contactors and motorstarters			
Electrical engineering	IEC 62271-106:2021	High-voltage switchgear and controlgear - Part 106: Alternating current contactors, contactor-based controllers and motor-starters	
Electrical engineering	UL347:2020 CSA C22.2 No. 253-16: 2020 NMX-J-564/106-ANCE: 2020	Medium-Voltage AC Contactors, Controllers, and Control Centers	

Testing field	Standard / In-House Procedure / Version	Title of Standard or In-House Procedure (Deviations / Modifications of Standard)	Test Range / Restrictions
Disconnectors and earthing switches			
Electrical engineering	IEC 62271-102:2018 STL Guide:2018	High-voltage switchgear and controlgear - Part 102: Alternating current disconnectors and earthing switches	
Electrical engineering	IEEE C37.30.1:2011	IEEE Standard Requirements for High-Voltage Switches	
Electrical engineering	IEEE C37.41:2016	IEEE Standard Requirements for High-Voltage Switches	
Switchgear and controlgear			
Electrical engineering	IEC 62271-200:2021	High-voltage switchgear and controlgear - Part 200: AC metal-enclosed switchgear and controlgear for rated voltages above 1 kV and up to and including 52 kV	
Electrical engineering	IEC 62271-201:2014	High-voltage switchgear and controlgear - Part 201: AC insulation-enclosed switchgear and controlgear for rated voltages above 1 kV and up to and including 52 kV	
Surge arresters			
Electrical engineering	IEC 60099-4:2014 GB/T11032-2020	Surge arresters - Part 4: Metal-oxide surge arresters without gaps for a.c. systems	
Electrical engineering	IEC 60099-8:2017	Surge arresters - Part 8: Metal-oxide surge arresters with external series gap (EGLA) for overhead transmission and distribution lines of a.c. systems above 1 kV	
Electrical engineering	IEEE Std C62.11:2012	IEEE Standard for Metal-Oxide Surge Arresters for AC Power Circuits (> 1 kV)	
Insulators, Bushings			
Electrical engineering	IEC 60383-2:1993	Insulators for overhead lines with a nominal voltage above 1000 V; part 2: insulator strings and insulator sets for a.c. systems; definitions, test methods and acceptance criteria	

Testing field	Standard / In-House Procedure / Version	Title of Standard or In-House Procedure (Deviations / Modifications of Standard)	Test Range / Restrictions
Electrical engineering	IEC/TS 60815-1:2008	Selection and dimensioning of high-voltage insulators intended for use in polluted conditions - Part 1: Definitions, information and general principles	
Electrical engineering	IEC/TS 60815-2:2008	Selection and dimensioning of high-voltage insulators intended for use in polluted conditions - Part 2: Ceramic and glass insulators for a.c. systems	
High-voltage test techniques			
Electrical engineering	IEC 60060-1:2010	High-voltage test techniques; Part 1: General definitions and test requirements	
Electrical engineering	IEC 60060-2:2010	High-voltage test techniques - Part 2: Measuring systems	
Electrical engineering	IEC 60270:2000+ AMD1:2015	High-voltage test techniques - Partial discharge measurements	Korrektur
Mechanical testings, environment- and guardtesting			
Electrical engineering	IEC 60529: 1989+ AMD1:1999+AMD2:2013	Degrees of protection provided by enclosures (IP code)	-
Electrical engineering	IEC 60068-2-1:2007	Environmental testing - Part 2-1: Tests - Tests A: Cold	
Electrical engineering	IEC 60068-2-2:2007	Environmental testing - Part 2-2: Tests - Test B: Dry heat	
Electrical engineering	IEC 60068-2-14:2009	Environmental testing - Part 2-14: Tests - Test N: Change of temperature	
Electrical engineering	IEC 60068-2-17:1994	Basic environmental testing procedures - Part 2: Tests - Test Q: Sealing	
Electrical engineering	ISO 3744: 2010	Acoustics - Determination of sound power levels of noise sources using pressure - Engineering method in an essentially free field over a reflecting plane	

Annex to the Accreditation Certificate D-PL-11055-10-00

Testing field	Standard / In-House Procedure / Version	Title of Standard or In-House Procedure (Deviations / Modifications of Standard)	Test Range / Restrictions
Electrical engineering	IEC/IEEE 62271-37- 082:2012 IEEE 62271-37-082:2012	High-voltage switchgear and controlgear - Part 37-082: Standard practice for the measurement of sound pressure levels on alternating current circuit-breakers	