



PROCESS INSTRUMENTATION

Do you know **if your flow readings are correct?**

Siemens is offering flow calibration services so you can be assured that you are getting the accuracy you require.

usa.siemens.com/flow-calibration

Demands on accuracy, reliability, and availability of measurement instruments are steadily increasing. Siemens Industry Services provides complete, traceable calibration of flow meters. Using flow calibration facilities certified to national and international standards, Siemens will ensure your flow meters are calibrated properly.

SIEMENS

Precise Flow Calibration, adaptable for your needs



Siemens Verificator with certified verification report

Advanced & Flexible Hardware

Siemens offers the ability to confirm the performance of our Magmeters with MAG5000 or MAG6000 transmitters while the flowmeter remains in-line using our independent and certified verifier.

But when a traceable calibration on a certified flow-rig is required Siemens offers calibration services covering our MAG1100, MAG3100, and MAG5100 sensors with MAG 5000, MAG6000, and MAG6000i transmitters, as well as the Transmag. Flowmeters can be sent in for recalibration as just the flow sensor, or as a complete sensor/transmitter combination.

A Wide Range of Sizes

Siemens will provide calibration for Magmeters up to 12 inch line sizes

Certificate Access

NIST or ISO traceable calibration certificates uploaded to global database for easy access.

Points of Calibration

Siemens can provide 1, 3, and 5 point calibrations

Extreme Precision

Siemens will certify our Magmeters to the original factory accuracy

If Flowmeter Cannot Be Calibrated

Once Siemens performs an evaluation of the flow sensor, if it is determined that the sensor cannot be calibrated to original factory performance, the customer will be contacted by Siemens Factory Service personnel and advised of the options for repair.

Verification Services

For less rigorous analysis, Siemens Magmeters with MAG5000 or MAG6000 transmitters can utilize the Siemens Verificator. This will electronically confirm that the flowmeter is operating within parameters that maintain the initial accuracy performance as installed. The Verificator provides a traceable certificate confirming the Magmeter's performance.

Ordering Calibration Services

Contact 1-800-333-7421 with any questions or to arrange for future calibrations of Siemens flow products.

Legal Manufacturer

Siemens Industry, Inc.
100 Technology Drive
Alpharetta, GA 30005
United States of America
Telephone: +1 (800) 365-8766
usa.siemens.com/pi
Order No.: PIFL-00122-0522

This document contains a general description of available technical options only, and its effectiveness will be subject to specific variables including field conditions and project parameters. Siemens does not make representations, warranties, or assurances as to the accuracy or completeness of the content contained herein. Siemens reserves the right to modify the technology and product specifications in its sole discretion without advance notice.