

# SIEMENS

*Ingenuity for life*



## Ideal for challenging installations

Trust the SITRANS MAG 5100W and MAG 8000 for proven accuracy in non-standard pipe configurations



The SITRANS F M MAG 5100W and MAG 8000 electromagnetic sensors from Siemens rise to virtually any challenge faced in the measurement of water and wastewater.

The MAG 5100W is a traditional externally powered electromagnetic flow meter designed for water and wastewater applications. The MAG 8000 is ideal for applications where external power is not available, such as remote pumping stations and field irrigation.

Designed for highly accurate measurement in low-flow conditions, these meters also stand up to direct burial, constant flooding and the wide range of harsh chemicals found in water based applications in many different industries.

# Performance Results

## Results

A reference test was first conducted by installing the MAG 5100W and MAG 8000 as recommended by Siemens for the best possible performance, with 5D upstream pipe and 3D downstream pipe from the sensor. The meters were then tested in various configurations that do not meet the suggested installation conditions. The results were consistent enough to allow acceptance by independent approval body to allow meters with these installation variations to be approved for an accuracy of  $\pm 2.0\%$  even with zero diameters upstream and downstream of straight run pipe.



This makes them a great choice for installations where other meters can't perform due to the lack of sufficient straight runs in approach and retreat piping.

The bottom line: no matter how demanding your water or wastewater installation may be, you can rely on the MAG 5100W and MAG 8000 to get the job done right.

There is no substitution for installing a flow meter following the guidelines for optimal performance. However, with a homogeneous fluid, when the optimal mechanical piping conditions don't exist or when the modification of the process piping is cost prohibitive, the ability to mount a meter in less than optimal conditions can offset the reduction in performance to 2%.



SITRANS MAG 5100W and MAG 8000 have been independently confirmed to operate in a variety of non-optimal piping arrangements and still provide acceptable accuracy while maintaining their exceptional repeatability specification. Other flow technologies, both solid state (no moving parts) and mechanical (moving parts) require upwards of 50 diameters upstream and 20 diameters downstream in order to operate within the same performance levels as the Siemens SITRANS MAG 5100W and MAG 8000 with zero up and downstream straight runs of piping.

When you look at which product to select when you don't have the ideal installation capability, consider the use of Siemens MAG 5100W and MAG 8000 versus the cost of major modifications to your process piping.

But their versatility doesn't end there. A series of tests were conducted by an independent approval body, a globally accredited agency which proved that the MAG 5100W and MAG 8000 are capable of exceptional accuracy even in nonstandard configurations with an insufficient straight run of pipe. Based on its demonstrated ability to perform in non-ideal conditions, the MAG 5100W and MAG 8000 have received approval for 2% accuracy custody transfer (MI-001) and non custody transfer applications for installation with zero diameter upstream pipe and zero diameter downstream straight run pipe from the sensor.

Siemens Industry, Inc.  
Process Industries and Drives  
100 Technology Drive  
Alpharetta, GA 30005  
1-800-365-8766

Subject to change without prior notice  
Order No.: PIFL-00093-0819  
All rights reserved  
© 2019 Siemens Industry, Inc.