

# Design in **perfection**

DELTA switches and sockets - meeting all requirements

siemens.com/delta



### More than just switches and sockets – the DELTA **design programs**

DELTA offers an abundant selection of designs, materials, and functions. From motion and smoke detection to shutter/blind and room temperature control, an entire spectrum of solutions and applications guarantees enhanced comfort and security. Integrated in the DELTA design programs, these functions merge seamlessly in new, renovated, or refurbished buildings.

#### Contents

Design and functionality in perfection	2
DELTA line	4
DELTA miro color	5
DELTA miro glass	6
DELTA miro aluminum	7
DELTA miro wood	8
DELTA style	9
DELTA profil	10
DELTA surface	11
i-system	12
DELTA USB sockets	13
Functions at a glance	14
GAMMA instabus	15

Program	DELTA line	DELTA miro color	DELTA miro glass	DELTA miro aluminum	DELTA miro wood	DELTA style	DELTA profil	DELTA surface
Number of frame colors	4	4	5	2	5	4	2	1
Number of insert colors	4	4	4	2	4	4	2	1
Multiple frames	1 to 5gang	1 to 5gang	1 to 5gang	1 to 5gang	1 to 4gang	1 to 3gang	1 to 3gang	1 to 3gang
Labeling field	X	Х	X	X	X	X	Х	X
Frames for horizontal and vertical mounting	X	х	х	x	х	х	х	X
Combinable with components from the i-system, including operator interfaces and SCHUKO® outlets	X	X	X	X	X	_	-	-
Set of seals for rockers and outlets for the IP44 degree of protection	X	X	X	X	X	X	_	X
IP44 (splash-proof version) and IP68 (pressure-watertight version)	_	_	_	_	_	_	_	X

### Comprehensive functions from the i-system

	_							
USB charger	x	x	x	Х	x	x	-	_
Communication	X	X	X	х	X	X	X	_
Data and voice networks	X	X	x	x	X	X	X	_
Time circuits	Х	Х	x	х	Х	X	х	_
Shutter/blind control	X	X	X	х	X	X	X	_
Room temperature control	Х	x	X	х	x	x	Х	_
Dimmer control	Х	Х	x	х	X	X	х	_
Motion detection	X	X	X	х	X	X	X	_
Connectable to GAMMA instabus	X	X	X	X	X	X	_	_

## Excellent switching with **DELTA**

Whether you're looking for a classic, modern, or exclusive design, a flexible system or high-quality material, our DELTA switch programs are versatile enough to satisfy any taste.

With the right design, it's possible to set stylish accents in every home environment. All the product ranges are compatible with GAMMA instabus, the future-proof electrical installation system for more comfort at home. This means that you aren't restricted in the choice of your favorite design.

Our pioneering design is founded on innovative, proven, high-quality technology. Our designers are masters at creating objects that convey the essence of a contemporary lifestyle, from form and function to structural design and the use of ecological materials.

Environmentally sound design is a fundamental principle of our product development process. It includes the selecting materials with the lowest possible pollutant content, economically using these materials, and developing appropriate recycling strategies.





#### A variety of products for high demands.

With its stylish array of designs and colors, our extensive product range offers you countless custom design options for skillfully enhancing the aesthetics of any room.

Thanks to our manufacturing expertise, we can also guarantee the high quality and long service life of our DELTA switches and sockets – from the individual parts right down to the finished product.

The DELTA switch and socket programs combine the most diverse design interfaces with innovative, safe technology and the largest possible choice of functions. The light switches are especially simple to install. Because the operator interfaces are easily replaced, safety is always maintained – even when tastes or the environment change. All Siemens sockets are certified for SCHUKO<sup>®</sup>.

For more information, watch our design and installation video at www.siemens.com/ delta



### DELTA line

#### A genuine classic. Timeless beauty.

Perfect proportions, an elegant look, and a sleek design – these are the key features of the DELTA line.

This switch range sets new standards in the language of design: narrow corner radii, precise outer edges, and a harmonious surface appearance. A special feature is the slim form. The switch blends timelessly into any interior design, supported by a modern range of product colors – titanium white, electrical white, aluminum metallic, and carbon metallic. So you can always stay flexible, right down the line.








### DELTA miro color

#### Focus on design. Pure beauty.

Optimal design – DELTA miro color makes it possible.

Ilf you want to furnish your entire house with a single switch line, a solution based on DELTA miro color is an exciting alternative – either alone or in conjunction with DELTA miro glass, wood, or aluminum.





### DELTA miro glass

For all those who love design. Something special.

Pure and simple design – that's the DELTA miro glass switch range. Sophisticated materials, clear-cut lines, and an incomparably slim form are the key features of these switches.

With the glass frame providing a unique showcase for the operator interface, DELTA miro glass stands out due to its elegant appearance. But that's not all: It also offers a host of functions. The DELTA miro glass range benefits from the components and broad functionality of the i-system. And you're entirely free to choose your favorite combination from the i-system's four rocker colors.



### DELTA miro aluminum

#### Graceful lines. Sleek design.

A timelessly sleek design in perfect harmony with your unique and elegant lifestyle.

At the office or at home, the graceful lines of this design range add to a stylish ambiance. Aluminum – a reusable, long-lasting material. From its engineering to its function and design, DELTA miro aluminum features a special surface appearance and the full range of i-system functions.









Nature*l* carbon metallic



7

### DELTA miro wood

#### Stylish accents. Natural appeal.

Design follows function. The choice of materials available for DELTA miro now matches the functional diversity of the i-system components.

Five solid-wood frames create rich opportunities in switch design. Whether the goal is to embellish your walls with a series of elegant details or to bring your light switches into line with the warm wood shades of your furniture – the sky's the limit. And it goes without saying that you can still enjoy the vast functionality of the i-system, including room temperature and shutter/blind control. As a natural product, wood can exhibit color differences and irregularities caused during its growth.







### DELTA style

### Clarity in form and function. Pure and simple design.

People who like clear-cut elegance are advised to opt for DELTA style, our designer series in the DELTA product range.

These switches combine an aesthetically pleasing design with exceptional functionality – minimalist, elegant, modern, and sensuous. At home or at work, it's a concept that never fails to impress. Pure and simple design.





### DELTA profil

#### Warm hues, harmonious shapes.

DELTA profil is a switch range that blends especially well into interior designs, whether it's in titanium white or silver.

These warm, bright hues are an excellent match for the curved lines of the switch. With this unique combination, DELTA profil fits perfectly into any ambiance.



### DELTA surface

#### Absolutely waterproof.

Whether they're in garages, utility rooms, laboratories, or workshops – as a waterproof and heat-resistant option in the DELTA series, products in the DELTA surface range provide perfect all-around protection for your electrical installation.

The splash-proof product range for damp locations and the pressure-watertight surface-mounting product range are designed for the harshest hot or cold environments. Along with their fire-retardant and impact-resistant polycarbonate casings, they guarantee your safety.





### i-system


#### Stay flexible!.

Maximum flexibility - the i-system makes it all possible. The i-system offers you a neutral, design-independent component pool with a broad range of functions.

You benefit from functional modules that can be installed in frames from the DELTA line and DELTA miro ranges. This means that you can easily change the shape, style, and color, because you don't have to decide in advance which design range you want to use.

The entire design range is available for all DELTA switches. The gap between the frame and rocker is always the same plus one insert fits all operator interfaces. This not only simplifies installation and helps prevent errors, it also ensures that existing installations can be retrofitted with new modular components any time that you happen to have a change in taste.

It also goes without saying that the DELTA product ranges are future-proof – and not just because of their environmentally sound design. All DELTA product ranges are also suitable for the GAMMA instabus Building Management System, the future-proof electrical installation system for greater comfort at home. Installing the insert is also extremely easy, safe, and fast, because it's equipped with a combination screw for Torx T10 and slotted screwdrivers - so you'll always have access to the right tool.





### DELTA USB sockets

#### Function and convenience in one connection.

The socket and power supply form a harmonious unit, whether they're in a bedroom, living room, or hotel room.

The DELTA double USB charger is designed for portable electronic devices that connect via USB 2.0 Type A plugs. This means that you can charge two devices simultaneously, regardless of where you are – in a hotel, having breakfast in your kitchen, or at work.


Smart and fleible charging: The multifunction DELTA SCHUKO<sup>®</sup> sockets permit the simultaneous charging of two USB devices like tablets, smartphones, and MP3 players, while your electric appliance is still plugged into the same socket.



### | Functions at a glance

#### Function meets design.

Switches and compact dual sockets



Shutter/blind controller	SCHUKO <sup>®</sup> dual socket	SCHUKO® dual socket
Easy to operate, convenient, and secure.	without frame	with frame
		17 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0

### GAMMA instabus

#### **Building management system.**

As diverse as the requirements for new buildings

They have to be attractively designed, highly functional, and economical in everyday use. They need to allow for flexible use of space and be adaptable to the wishes of individual users. The lighting, sun shading, and indoor climate have to merge convenience with energy efficiency. Today all these requirements can be met, thanks to GAMMA instabus.





#### Design meets functionality

- Every DELTA product range is suitable for GAMMA instabus building control – the future-proof electrical installation system for greater comfort at home. This means that you aren't restricted in the choice of your favorite design.
- Simple and intuitive operation
- Pushbutton and room temperature controller harmoniously matched to the electrical room installation
- Can be combined with different design frames in different colors, shapes, and materials
- Based on the worldwide KNX standard



	1	1	
DELTA miro aluminum	DELTA miro glass	DELTA line	DELTA miro glass
UP 587 pushbutton with text display	UP 587/1 pushbutton with text display	UP 222/3 dual pushbutton with status LED	UP 237K room temperature controller



#### Publisher

Siemens AG Smart Infrastructure Low Voltage Products Von-der-Tann-Strasse 30 90439 Nuremberg Germany

For the U.S. published by Siemens Industry Inc. 100 Technology Drive Alpharetta, GA 30005 United States

Article No. SIEP-B10223-00-7600 TH 477-190747 WS 11191.5 Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.

All product designations may be trademarks or other rights of Siemens AG, its affiliated companies or other companies whose use by third parties for their own purposes could violate the rights of the respective owner.