

NOTES:

- 1. SIZE: 3.75" X 6.00" .125 rcr
- 2. MATERIAL: Semi-Gloss Paper
- 3. INK COLOR: Black

To: SIEMENS
 Attn:
 Fax:

SIEMENS

Enclosed Switch Plug Fuse Type
 General Duty

Catalog Number Enclosure
LF111NR **Type 3R**

| Amperes 30 | <table style="width: 100%; border-collapse: collapse;"> <tr> <th colspan="3">Horsepower Rating</th> </tr> <tr> <th style="width: 33%;">Volts-PH</th> <th style="width: 33%;">Std.</th> <th style="width: 33%;">Max.</th> </tr> <tr> <td>120 AC-1Ø</td> <td>½</td> <td>2</td> </tr> </table> <p style="font-size: 0.8em; margin: 0;">The starting current of motors more than the standard horsepower rating may require the use of fuses with appropriate time delay characteristics. Continuous load current not to exceed 80 percent of the rating of fuses employed in other than motor circuits.</p> | Horsepower Rating | | | Volts-PH | Std. | Max. | 120 AC-1Ø | ½ | 2 |
|----------------------|--|-------------------|--|--|----------|------|------|-----------|---|---|
| Horsepower Rating | | | | | | | | | | |
| Volts-PH | Std. | Max. | | | | | | | | |
| 120 AC-1Ø | ½ | 2 | | | | | | | | |

Wire Connector Information:
 Line / Neutral Terminals: **USE 14-6 Cu/ 12-6 Al 60°/75° C WIRE**
 Load Terminals: **USE 14-8 Cu/ 12-8 Al 60°/75° C WIRE**

| | | | |
|-----------------|------------|------------|------------|
| WIRE SIZE: | 14-10 AWG | 8 AWG | 6 AWG |
| NOMINAL TORQUE: | 15 LB. IN. | 18 LB. IN. | 27 LB. IN. |

Fuse & Short Circuit Information:
 This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, rms symmetrical, **240** Volts Maximum. (120 Volts Max. on single pole devices.)

Accessories and Replacement Parts:
Service Equipment:
 To bond enclosure to neutral, use No. 10 screw provided. Force the screw through the aluminum seal.
Hub Information: Catalog Number: HA075S HA100S HA125S
¾" 1" 1-¼"
 Use closure plate screws provided, to mount hubs.
Equipment Ground Bar Kit: GSGK60. USE **Cu/Al 60°/75° C WIRE**
 WIRE SIZE: 14-10 AWG 8 AWG 6 AWG
 NOMINAL TORQUE: 35 LB. IN. 40 LB. IN. 45 LB. IN.

⚠ DANGER

HAZARDOUS VOLTAGE. WILL CAUSE DEATH OR SERIOUS INJURY.

Turn off switch before removing or installing fuses. Turn off power ahead of switch before doing work inside. Close cover before turning power on.

This device has been inspected and tested.
 Inspection Record No. _____

LISTED
ENCLOSED SWITCH
Issue No. AL-265
File No. E4776

Pc. No. 410384C01

Siemens Energy & Automation, Inc.
Bellefontaine, Ohio 43311 U.S.A.
Assembled in Mexico (E)

6.00"

3.75"

.125" RCR

- OK to print
 - OK to Print with corrections as marked
 - Make corrections, resubmit corrected proof
- Job will not be printed unless approved by customer.

| | | | | | |
|-------------|-------|---------------|-----------------|------------------|-----|
| Artwork By: | Date: | AUTHORIZED BY | DATE | PART NUMBER | REV |
| Proofer: | Date: | | 08/03/04 | 410384C01 | |