

REVISION	DATE	BY	DATE	BY
		DRAWN	16/02/02	PP
		CHEK'D		
		VERIF'D		

Confidential - Property of
Siemens Industry, Inc.

CUSTOMER	
ORDER NO.	DWG. NO.
	3F1Y045K13FCD16 SH 1 OF 2

SIEMENS

CATALOG NO. 3F1Y045K13FCD16
SERIAL NO. SERIES H
45 kVA **60** Hz **3** PHASE
4.1 % IMP AT **135** °C

115 °C RISE	30 °C AVG. AMBIENT
220 °C TEMP CLASS	40 °C MAX. AMBIENT
PRIMARY (H1 H2 H3)	480V V 10 kV BIL
SECONDARY(X1 X2 X3)	240V V 10 kV BIL

WINDING MATERIAL **CU**
ENCLOSURE TYPE **3R** WEIGHT **450** LBS
ENERGY EFFICIENCY **EXCEEDS CSA** DOE 10 CFR PART 431:2016
C802.2-2012

SPACINGS BETWEEN ANY VENTILATED ENCLOSURE, PANEL AND ANY ADJACENT WALL SHALL BE A MINIMUM OF 3 INCHES
X6=120V C.T., 5% OF KVA RATING MAXIMUM
ELECTROSTATIC SHIELD

SUITABLE FOR NONSINUSOIDAL CURRENT LOAD WITH K-FACTOR NOT TO EXCEED K-13
SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS
BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION MANUAL

NEMA Class **ANN** Dry Type Transformer
Siemens Industry, Inc. Norcross, GA dsu0087e



VOLTS
504
492
480
468
456
444
432



HAM5008
CONNECT
1 2 3 4 5 6 7

TYPE K



LISTED




DRY TYPE TRANSFORMER
7705 E112313

LR 3902

SEISMIC QUALIFICATIONS, FLOOR MOUNT ONLY
OSP-0136-10 IBC 2012/ASCE 7-10
SDS<=2.0g Z/h=1 Ip=1.5



3F1Y045K13FCD16



All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY – OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #14-2 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR 250MCM-6 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Confidential – Property of
Siemens Industry, Inc.

REVISION	DATE	BY	DATE	BY	CUSTOMER
			DRAWN 16/02/02	PP	
			CHEK'D		
			VERIF'D		
					ORDER NO.
					DWG. NO. 3F1Y045K13FCD16
					SH 2 OF 2