

Flat Rate Repair Structure for Out of Warranty				
Product Line	Product	Repair Price Canadian \$\$	Rush Charge	Total Incl Rush Canadian \$\$
ULTRASONICS	<b>Continuous Level</b>			
	7ML1810 - AO10	Contact Factory		
	7ML1025/1028 - HYDRO +	\$650.00	\$130.00	\$780.00
	7ML1022 - HYDRO SM	No repair		
	7ML1034 - HYDRORANGER	\$650.00	\$130.00	\$780.00
	7ML 5034 - HYDRORANGER	\$650.00	\$130.00	\$780.00
	7ML1016-1 - MINIR + /RM/PM	No repair		
	7ML1020 - MULTI+SM	No repair		
	7ML1033 - MULTIRANGER	\$650.00	\$130.00	\$780.00
	7ML5033 - MULTIRANGER	\$650.00	\$130.00	\$780.00
	7ML1002 - OCM	Contact Factory		
	7ML1010 - CRANERANGER	Contact Factory		
	7ML1013 - DPS300	Contact Factory		
	7ML1001 - ENVIRORANGER	\$650.00	\$130.00	\$780.00
	PROGL	No repair		
	7ML1811 - SAM20	Contact Factory		
	TEMPSENS	No repair		
	7ML1004 - SPL /DPL	\$650.00	\$130.00	\$780.00
	7ML5004 - SITRANS LU 01 / LU 02	\$650.00	\$130.00	\$780.00
	7ML5007 - SITRANS LU 10	\$650.00	\$130.00	\$780.00
	7ML1007 - XPL +	\$650.00	\$130.00	\$780.00
	7ML60 - LT500	\$650.00	\$130.00	\$780.00
	7ML5050 - LUT400	\$650.00	\$130.00	\$780.00
	<b>Transducers</b>			
	LR SERIES	No repair		
	7ML1100 - STH	No repair		
	7ML1136 - XCT12	No repair		
	7ML1132 - XCT8	No repair		
	7ML1105/1106/1109 - XRS5	No repair		
	7ML1170 - XPS10F	No repair		
	7ML1115 - XPS10	No repair		
	7ML1118/1161/1171 - XPS15	No repair		
	7ML1123/1155 - XPS30	No repair		
	7ML1127 - XPS40	No repair		
	7ML1158 - XPS40C	No repair		
	<b>Probe</b>			
	7ML5221 - PROBE LU	No repair		
	7ML51 - LU240	No repair		
	7ML5201 - LU150	No repair		
	7ML5202 - LU180	No repair		
	7ML5430 - PROBE LR	No repair		
	7ML1201 - PROBE2W	No repair		
	7ML1201 - PROBE3W	No repair		
	7ML1201 - PROBEIS	No repair		
	7ML1201 - PROBEEXT	No repair		
	7ML1201 - HPROBE	No repair		
	<b>Point level</b>			
	STOCKTROL	Contact Factory		
	7ML1510 - POINTEK ULS	No repair		
	MASS DYNAMICS	<b>Continuous Weighing</b>		
7MH7164/7MH7175 - PLS/VLS		Contact Factory		
COMPUSCALE		No repair		
7MH7122 - MSI (Global)		Contact Factory		
7MH7125 - MCS (Global)		Contact Factory		
7MH7120/7123 - MUS (Global)		Contact Factory		
7MH7177 - WS300 Speed Sensor		Contact Factory		
7MH7130 - MD256 repl by WS300		Contact Factory		
7MH7132 - MD256 repl by WM100		Contact Factory		
7MH7158 - WM100		Contact Factory		
7MH7134 - RBSS		Contact Factory		
SF500 - 7MH7156		\$650.00	\$130.00	\$780.00
7MH7150 - BW100		No repair		
7MH7152 - BW500		\$650.00	\$130.00	\$780.00
7MH7110 - ILE37 (Global)		Contact Factory		
7MH7112 - ILE61 (Global)		Contact Factory		
7MH7100 - MILLFLO (Global)		Contact Factory		
LOADCELL		No repair		
WF400 (Global)		Contact Factory		
WF600 (Global)		Contact Factory		
WF800 (Global)		Contact Factory		
WF1200 (Global)		Contact Factory		
WFCUST (Global)		Contact Factory		
WFSP (Global)		Contact Factory		
7MH7180 - WW100		Contact Factory		
WW200		Contact Factory		
WW300		Contact Factory		
<b>Process Protection</b>				
7MH7144 - MFA4P		\$250.00	\$50.00	\$300.00
7MH7142 - MILLPULSE		No repair		
MSP12 - 7MH7146		No repair		
PREAMP		No repair		
XPP5		No repair		
ZEROSS		No repair		
7MH7562 - SENACOCU		\$250.00	\$50.00	\$300.00
7MH7560 - AS100		No repair		

Flat Rate Repair Structure for Out of Warranty				
MICROWAVE	<b>Radar</b>			
	7MLS30 - LR100	Contact Factory		
	7MLS31 - LR110	Contact Factory		
	7MLS32 - LR120	Contact Factory		
	7MLS33 - LR140	Contact Factory		
	7MLS34 - LR150	Contact Factory		
	7MLS422 - LR200	No repair		
	7MLS423/5424/5425 - LR200	\$900.00	\$180.00	\$1,080.00
	7MLS431 - LR250	\$900.00	\$180.00	\$1,080.00
	7MLS432 - LR250 Flange Encap Ant.	\$900.00	\$180.00	\$1,080.00
	7MLS433 - LR250 ENCAPHGA	\$900.00	\$180.00	\$1,080.00
	7MLS427 - LR260	\$900.00	\$180.00	\$1,080.00
	7MLS413/5412/5411 - LR 300	No repair		
	7MLS420/5421 - LR400	No repair		
	LR400 Retro fit to LR460	\$900.00	\$180.00	\$1,080.00
	7MLS426 - LR460	\$900.00	\$180.00	\$1,080.00
	7MLS440 - LR560	\$900.00	\$180.00	\$1,080.00
CAPACITANCE	<b>Capacitance</b>			
	7MLS501/5610 - CLS100	No repair		
	7MLS502/5504/5505 - CLS200	No repair		
	7MLS630/5631/5632/5633/5634/5640/5641/5642/5643/5644 CLS200	No repair		
	7MLS503/5506/5507/5508 - CLS300	No repair		
	7MLS650/5651/5652/5660/5661/5662 - CLS300	No repair		
	7MLS601/5602/5603/5604 - CLS500	Contact Factory		
	7MLS605/5606 - LC300 SITRANS	Contact Factory		
	7MLS670/5671/5672/5673 - LC300	Contact Factory		
	7MLS511, 5512, 5513, 5514, 5515, 5516, 5517, 5518- LC500 SITRANS	Contact Factory		
	Third party products	<b>Hardware</b>		
LEVELWATCH		No Repair		
7MLS710,5712,5714, 5725,5726, 5727,5728,5730 - LPS200		Contact Factory		
7MLS720,5722, 5724,5731,5732, 5733, 5734 - LVS 200		Contact Factory		
7MLS735 - LVS 100		Contact Factory		
7MLS745 - LVL100		Contact Factory		
7MLS746, 5747 - LVL 200		Contact Factory		
VLS200 - 7MH7175		Contact Factory		
7ML1300,1301,1302,1303,1304, 1305 - LG 200		Contact Factory		
PLS200 - 7MH7164/6/8		Contact Factory		
SMARTLINX		No Repair		
VS-100 - 7ML1030		Contact Factory		

Surcharges	
Rush Charge	20% of Repair Costs
Evaluation Fee	\$200.00 CAD
- Includes No Faults Found	\$200.00 EUR
	\$200.00 USD
ReStocking Charge	based on the Siemens credit table