


## WP Series: Ring Style

### Uni-PAK Metering

#### Data Sheet



#### Features:

- Individual split cover types
  - Ring
  - Ringless
  - Barrel lock compatibility
- UL listed for 60/75° C conductors. See equipment markings for application
- For small apartment buildings, small professional and commercial buildings
- Completely self-contained meter centers
- Two to six 125A and 225A breaker positions
- Outdoor surface mounted enclosures
- Compact, pre-bussed, easy to handle, hang and wire
- Barriercd, sealable compartment for unmetered current carrying parts
- AL/CU lay-in lugs, except two positions 125A units
- Top or bottom feed
- Bottom and rear branch wiring exits (Neutral and ground at bottom only)
- ANSI #61 light gray electrodeposited paint on zinc-coated G90 steel
- Factory or Field installable 5th jaw kit
- Factory or Field installable horn bypass (ringless style only)

### Ring Style Uni-PAK 120/240V 1 Phase, 3 Wire

Maximum Tenant Main <sup>①</sup>	Bus Amperage	Meter Positions Per Pak	Old Catalog Number <sup>②</sup>	NEW Catalog Number	Breaker Provision	Max. AIC	Dimensions <sup>①</sup>			5th Jaw Assembly	Line Lugs Wire Range <sup>①</sup>
							Height	Width	Depth		
125	200	2	SP2211	WP2211	QP, QPH, HQP, MP-T, MP-HT, MP-MT	65,000	26.20	13.80	5.81	ECMF5	#6-300 kcmil
	300	3	SP3311	WP3311			38.75	25.42	#2-600 kcmil		
	400	4	SP4411	WP4411			47.75	38.95	1/0-750 kcmil CU-AL or (2) 1/0-250 AL or (2) 1/0-3/0 CU		
		5	SP4511	WP4511			38.75				
	500	4	SP5411	WP5411			47.75	26.47	(2) #2-600 kcmil		
	600	5	SP6511	WP6511			38.75	39.01			
225	400	2	SP4212	WP4212	QP, QPH, HQP, MP-T, MP-HT, MP-MT, QS, QSH, QSHH, HQS, HQSH	100,000	29.75	28.53	7.56	ECMF5	1/0-750 kcmil CU-AL or (2) 1/0-250 AL or (2) 1/0-3/0 CU
		3	SP4312	WP4312			38.75				
	600	4	SP4412	WP4412			47.75	29.59	(2) #2-600 kcmil		
		5	SP6512	WP6512			38.78	46.22			
	800	6	SP8612	WP8612				51.03	(2) 1/0-750 kcmil or (4) 1/0-250 AL or (4) 1/0-3/0 CU		
	1000	NA	WP10612	(3) #2-500 kcmil							

① Dimensions shown are representative of outside box length, width, and depth and do not include allowances for mounting bumps, endwalls, covers, hubs or hardware protrusions. Dimensions are subject to change.

② Dimensions, ratings, and technical information shown are for WP series PAK only. Consult the 2007-2008 Speedfax for information on SP series.

### Ringless Style Uni-PAK 120/240V 1 Phase, 3 Wire, No Bypass

Max. Tenant Main	Bus Amperage	Meter Positions Per Pak	Old Catalog Number <sup>②</sup>	NEW Catalog Number	Breaker Provision	Max. AIC	Dimensions <sup>①</sup>			5th Jaw Assembly	Horn Bypass Kit	Line Lugs Wire Range
							Height	Width	Depth			
125	200	2	SP2211RJ	WP2211RJ	QP, QPH, HQP, MP-T, MP-HT, MP-MT	65,000	26.26	13.79	5.81	INCL. 9:00 Factory 6:00 Field	ECMFH	#6-300 kcmil
	300	3	SP3311RJ	WP3311RJ			38.75	25.42	#2-600 kcmil			
	400	4	SP4411RJ	WP4411RJ			47.75	38.95	1/0-750 kcmil CU-AL or (2) 1/0-250 AL or (2) 1/0-3/0 CU			
		5	SP4511RJ	WP4511RJ			38.75					
	500	4	NA	WP5411RJ			47.75	26.47	(2) #2-600 kcmil			
	600	5	SP6511RJ	WP6511RJ			38.75	39.01				
225	400	2	SP4212RJ	WP4212RJ	QP, QPH, HQP, MP-T, MP-HT, MP-MT, QS, QSH, QSHH, HQS, HQSH	100,000	29.75	28.53	7.56	INCL. 9:00 Factory 6:00 Field	ECMFH	1/0-750 kcmil CU-AL or (2) 1/0-250 AL or (2) 1/0-3/0 CU
		3	SP4312RJ	WP4312RJ			38.75					
	600	4	SP4412RJ	WP4412RJ			47.75	29.59	(2) #2-600 kcmil			
		5	SP6512RJ	WP6512RJ			38.75	46.22				
	800	6	NA	WP8612RJ				51.03	(2) 1/0-750 kcmil or (4) 1/0-250 AL or (4) 1/0-3/0 CU			
	1000	NA	WP10612RJ	(3) #2-500 kcmil								

① Dimensions and information shown are for WPXXX units. For old style information, please see the 2008 Speedfax.

### Ringless Style Uni-PAK 120/240V 1 Phase, 3 Wire, Horn Bypass

Max. Tenant Main <sup>①</sup>	Bus Amperage	Meter Positions Per Pak	Old Catalog Number <sup>②</sup>	NEW Catalog Number	Breaker Provision	Max. AIC	Dimensions <sup>①</sup>			5th Jaw Assembly	Line Lugs Wire Range	
							Height	Width	Depth			
125	200	2	SP2211RJB	WP2211RJB	QP, QPH, HQP, MP-T, MP-HT, MP-MT	65,000	26.26	13.79	5.81	INCL. 9:00 Factory 6:00 Field	ECMFH	#6-300 kcmil
	300	3	SP3311RJB	WP3311RJB			38.75	25.42	#2-600 kcmil			
	400	4	SP4411RJB	WP4411RJB			47.75	38.95	1/0-750 kcmil CU-AL or (2) 1/0-250 AL or (2) 1/0-3/0 CU			
		5	SP4511RJB	WP4511RJB			38.75					
	500	4	NA	WP5411RJB			47.75	26.47	(2) #2-600 kcmil			
	600	5	SP6511RJB	WP6511RJB			38.75	40.00				
225	400	2	SP4212RJB	WP4212RJB	QP, QPH, HQP, MP-T, MP-HT, MP-MT, QS, QSH, QSHH, HQS, HQSH	100,000	29.75	28.53	7.56	INCL. 9:00 Factory 6:00 Field	ECMFH	1/0-750 kcmil CU-AL or (2) 1/0-250 AL or (2) 1/0-3/0 CU
		3	SP4312RJB	WP4312RJB			38.75					
	600	4	SP4412RJB	WP4412RJB			47.75	29.59	(2) #2-600 kcmil			
		5	SP6512RJB	WP6512RJB			38.75	46.22				
	800	6	NA	WP8612RJB				51.03	(2) 1/0-750 kcmil or (4) 1/0-250 AL or (4) 1/0-3/0 CU			
	1000	6	NA	WP10612RJB			(3) #2-500 kcmil					

① Dimensions and information shown are for WPXXX units. For old style information, please see the 2008 Speedfax. ② These units are for specific utilities only. Please contact sales office for more information.

**Siemens Industry, Inc.**  
**5400 Triangle Parkway**  
**Norcross, GA 30092**

**1-800-241-4453**  
**info.us@siemens.com**

Order No.: RPFL-UPKWP-0814 | Printed in USA |  
 © 2014, Siemens Industry, Inc.

**www.usa.siemens.com/residential**

The information provided in this flyer contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.

All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.