


SIEMENS

Ingenuity for life



Processes require precision

Reliable, low-maintenance pressure
measurement with SITRANS P

siemens.com/pressure-measurement

Pressure measurement under control


It's impossible to imagine today's process industries without modern measurement technology. Each industry has its own specific demands, whether they're requirements for safety-related devices or harsh, rugged environmental conditions. The SITRANS P family offers the right portfolio for your applications.

Uncompromising precision

SITRANS P pressure transmitters are a complete family of measuring instruments for measuring gauge, differential, and absolute pressure that includes a range of performance values, load capacities, and materials. In addition to high measuring accuracy and ruggedness, the modular system features superb operating convenience and functionality as well as an ideal safety concept. Whether it's international approvals or industry standards, our transmitters meet the challenges presented by increasingly complex tasks in the process industries.

Safety included

You can select device versions that also offer comprehensive safety features. Warnings and alarms signal critical measured values for plant monitoring, while service or calibration intervals can be displayed predictively through self-diagnostics based on a maintenance scheduler.



Configure your devices using our PIA Portal:
pia-portal.automation.siemens.com



Benefits at a glance

- High process quality thanks to reliable measured values, even after years of operation
- Superior communication capabilities based on industry standards such as 4...20mA, HART®, PROFIBUS PA, and FOUNDATION Fieldbus
- Seamless integration in SIMATIC PCS 7 thanks to specific faceplates and special support from the SIMATIC PDM (Process Device Manager) central maintenance station
- Support for parameterization, commissioning, diagnostics, and maintenance for all current process control systems thanks to EDD, DTM, and FDI packages
- Devices for SIL applications up to Level 2/3 can be used
- Rugged enough for use in difficult environmental conditions



SITRANS P500



SITRANS P420



SITRANS P320

Premium

Advanced

Benefits at a glance

- All applications supported thanks to a highly diverse portfolio
- Meet all current explosion protection requirements
- High product variance thanks to standard options and customizations
- A variety of materials and process connection options available, including stainless-steel enclosure versions
- Expanded diagnostics
- Maintenance benefits



SITRANS P Compact

Basic

SITRANS P

pressure measurement

For gases, liquids, and paste-like media, the gauge pressure, absolute pressure, and differential pressure must be measured constantly to detect values that are too low or a potential overload. Whether for pipelines, valves, or reactors, the SITRANS P transmitter family offers the right solution for every application.

The most important factor in selecting the right pressure transmitter is the required accuracy of the measuring range. SITRANS P transmitters offer a variety of choices from 0.03 percent to 0.3 percent. They're suitable for safety-related applications, with certifications according to SIL2 and SIL2/3.

Numerous bus systems for communication are also supported, including HART®, PROFIBUS PA, and FOUNDATION Fieldbus. In addition, the transmitters have all the most current approvals and certificates. Our pressure measuring devices give you the instrumentation reliability you need to meet your own specific requirements.



SITRANS P220 / P210 / P200

SITRANS P300

SITRANS P280

SITRANS LH100

SITRANS LH300

Devices for industry-specific applications

Communicating digitally

Distributed automation solutions based on open fieldbuses are now standard in many areas of the manufacturing and process industries. That's because the benefits of digital communication can be maximized in combination with fieldbuses, including transmission of measured values that retain the original accuracy, diagnostic options, and remote parameterization.

All the data at a glance

Thanks to modern fieldbus communication, field devices can be optimally integrated into the overall plant. Process and diagnostic data can be transferred from smart measuring devices to the control desk as well as to the control or maintenance system. An additional benefit: When the devices are integrated into PCS 7 Asset Management, users can access diagnostic information at all times, and can thus optimize plant maintenance and prevent downtimes. If desired, the data can be uploaded to MindSphere, the open cloud solution, for comprehensive analysis.



Remote safety handling

Digital transfer enables centralized SIL commissioning and validation – for example, from the control desk, without on-site device operation. Time saved through remote safety handling results in significantly reduced commissioning costs.



Ready for digitalization

With trend recording, 1.500 measured values are stored directly in the pressure transmitter. Thanks to limit monitoring and event counters, limit violations are recorded and displayed as a specific message, both on the device and in the control system.

Focus on the process industries



Safety is integrated

Stringent safety requirements must be met in all areas and sectors of the process industries. One example is chemicals, and our portfolio for pressure measurement unequivocally satisfies the high demands of the chemical industry (SIL 3). Thanks to comprehensive diagnostic functions, you always know whether your process is running according to plan and can intervene and correct it if necessary, for example in reactors. They are part of the overall plant and must be seamlessly integrated into the process for maximum safety, efficiency, and availability. Interventions such as filling, heating, cooling, mixing, and the monitoring of all process conditions are performed on an ongoing basis. In addition, parameters such as pump performance, temperature, energy consumption, and emissions must be measured, analyzed, and monitored.

Product range for your application

SITRANS P420

- High measurement accuracy of 0.040%
- Developed according to IEC61508 standards for SIL2/3
- Improved HMI display: larger, new and improved display with NAMUR NE107
- 4-key operation
- Remote safety handling
- Ready for digitalization

Industry: chemical, oil & gas, energy, shipbuilding, mechanical engineering



SITRANS P500

- Maximum measurement accuracy for highest precision requirements
- Reduction of storage costs with a turndown ratio of 200:1
- Reduction of maintenance costs due to high long-term stability
- Easy operation using the 3-key operating design and graphics-capable display

Industry: energy, chemical, oil & gas



SITRANS P200/210/220

A series for all pressure types:

- P200: gauge and absolute pressure with ceramic diaphragm for medium measuring ranges (up to 60 bar)
- P210: gauge and absolute pressure with stainless-steel diaphragm for low measuring ranges (up to 600 mbar)
- P220: gauge and absolute pressure with fully welded stainless-steel diaphragm for high measuring ranges (up to 1000 bar)

Industry: mechanical engineering, shipbuilding, energy



SITRANS P320

- High measuring accuracy of 0.065%
- Developed according to IEC61508 standards for SIL2/3
- Improved HMI display: larger, new and improved display with NAMUR NE107
- 4-key operation
- Remote safety handling

Industry: chemical, oil & gas, energy, shipbuilding, mechanical engineering, water/wastewater





SITRANS P300

- Designed for hygienic applications and available with more than 90 process connections
- Ideally suited for external cleaning with high protection classes IP68 and IP69K
- Features all current hygiene, material, and calibration certificates
- Low measurement errors, even at high temperatures

Industry: food & beverage and pharmaceuticals

SITRANS P Compact

- Features a wide range of aseptic process connections
- Space-saving transmitter thanks to compact enclosure
- Easy cleaning
- Process temperatures up to 200 °C possible

Industry: food & beverage and pharmaceuticals



SITRANS LH100, LH300

- Slim design with 23.4 mm diameter allows installation in pipes with 1" inner diameter
- Easy and safe installation even without cable socket thanks to built-in humidity filter in the cable
- Resistant to harsh environmental conditions due to the piezoresistive ceramic sensor
- SITRANS LH300: outer diameter of 26 mm

Industry: water/wastewater



SITRANS P280

- Transmits measured process variables, diagnostic information, parameters, and functions via radio
- Low power consumption due to high-capacity battery with a battery life of up to five years
- Flexible, easy configuration via HART® or the 3 pushbuttons and functional display
- Particularly suitable for applications in remote sections of the plant as well as moving or rotating equipment

Industry: chemical, water/wastewater, energy



Accessories

Remote seal

- High variance to meet all the requirements of each industry
- Wide range of diaphragm materials ensures excellent chemical resistance to medium

Aperture measurements

- Suitable for measuring high temperatures and pressure
- Can be combined with SITRANS P500, P410, P DS III, P310

Valves and valve blocks

- Save time with pre-mounted valve block
- Entire unit is seal-tested under pressure



Technical data



Type	SITRANS P500	SITRANS P420	SITRANS P320	SITRANS P300
	Premium	Advanced		Hygiene
Brief description	Digital pressure transmitter for measurement of differential pressure, level, and flow with highest accuracy	Digital pressure transmitter as "high performance" version of the P320 for gauge and differential pressure measurements	Digital pressure transmitter for measurement of gauge pressure, absolute pressure, differential pressure, flow, and level	Digital pressure transmitter for complex hygienic applications
Pressure types	Differential pressure	Gauge pressure, absolute pressure, differential pressure	Gauge pressure, absolute pressure, differential pressure	Gauge pressure, absolute pressure
Measuring span	1 mbar to 32 bar	1 mbar to 700 bar	1 mbar to 700 bar	10 mbar to 400 bar
Communication	4...20 mA/HART®	4...20 mA/HART®, PROFIBUS PA, FOUNDATION Fieldbus (in preparation)	4...20 mA/HART®, PROFIBUS PA, FOUNDATION Fieldbus (in preparation)	4...20 mA/HART®, PROFIBUS PA, FOUNDATION Fieldbus
Accuracy¹⁾	0.03 %	0.04 %	0.065 %	0.075 %
Max. Turndown	200:1	100:1	100:1	100:1
Long-term stability	0.05%/5 years	0.125%/5 years ²⁾	0.125%/5 years ²⁾	0.25%/5 years
Measured medium temperature	−40 °C to +125 °C	−40 °C to +100 °C	−40 °C to +100 °C	−40 °C to +200 °C
Certificates/approvals	ATEX, Exia/ib, Exd, ..., FM is/xp, CSA is/xp, NEPSI, SIL, ...	ATEX, Exia/ib, Exd, ..., FM is/xp, CSA is/xp, NEPSI, SIL, ...	ATEX, Exia/ib, Exd, ..., FM is/xp, CSA is/xp, NEPSI, SIL, ...	ATEX, Exia / ib, FM is/xp, CSA is/xp, NEPSI, ...
Diaphragm materials	Stainless steel, Hastelloy, tantalum, Monel	Stainless steel, Hastelloy, tantalum, Monel, gold	Stainless steel, Hastelloy, tantalum, Monel, gold	Stainless steel, Hastelloy
Special features		Remote Safety Handling, Ready for Digitalisation	Remote Safety Handling	

› www.siemens.com/sitransp500

› www.siemens.com/sitransp420


› www.siemens.com/sitransp320

› www.siemens.com/sitransp300

1) Conformity error according to IEC 60770-1

2) Depending on the version

3) WirelessHART® requires no downscaling



SITRANS P Compact	SITRANS P200/210/220	SITRANS LH100	SITRANS LH300	SITRANS P280
Single-range transformer				
Pressure transmitter for hygienic applications for measuring gauge and absolute pressure	Compact single-range transmitter for measuring absolute and gauge pressure	Pressure transmitter for measuring hydrostatic levels	Submersible sensor for hydrostatic level measurement	WirelessHART® pressure transmitter for gauge and absolute pressure
Gauge pressure, absolute pressure	Gauge pressure, absolute pressure	Level	Level	Gauge pressure, absolute pressure
0 bar to 40 bar	100 mbar to 1000 bar	0...3 mH ₂ O to 0...20 mH ₂ O	0 – 1 mH ₂ O to 0 – 40 mH ₂ O	0 bar to 320 bar
4...20 mA; 0...20 mA	4...20 mA	4...20 mA	4...20 mA	WirelessHART®
0.2 %	0.25 %	0.3 %	0.15 %	0.25 %
–	–	–	–	1:1 ³⁾
0.2%/year	0.25%/year	0.25%/year	0.15%/year	0.25%/year
–10 °C to +200 °C	–30 °C to +120 °C	–10 °C to +80 °C	–10 °C to +80 °C	–40 °C to +85 °C
ATEX, Exib	ATEX, Exia, EAC, GL, BV, ABS, UL	ATEX, Exia, IEC Ex, EAC, UL, WRAS	ATEX, Exia, IEC Ex, EAC, UL, WRAS	R & TTE, FCC CSA General purpose
Stainless steel	Ceramic, stainless steel	Ceramic	Ceramic	Ceramic

› www.siemens.com/sitranspcompact

› www.siemens.com/sitransp200

› www.siemens.com/sitranslh100

› www.siemens.com/sitranslh300

› www.siemens.com/sitransp280

Siemens Ltd.

Digital Industries
Process Automation
R&D Technology Centre
Thane Belapur Road Kalwa,
Thane – 400 601
For more information call us
on 1800 209 1800

For new enquiries, life cycle support for products,
systems and solutions, call us at 1800 208 3000 or
email us at pisupport.in@siemens.com

Product upgradation is a continuous process. Hence, data in
this leaflet is subject to change without prior notice. For the
latest information, please get in touch with our Sales Offices.

www.siemens.co.in

