


LOOKING ON FRONT OF RELAY

**NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED**

2112W50042

**CREATED 04/05/2020
WORKS STANDARD
IF IN DOUBT ASK**



ASSEMBLY WIRES USED	
a	2107B10001 16 OFF
b	2107B10002 4 OFF
c	2107D10169 2 OFF
d	2107B10003 1 OFF
e	2107D10165 3 OFF

RESET KIT	REFER TO ENGINEERING				SOLKIT: 36V	REFER TO ENGINEERING
RL2 COIL					2112G20031	
RL1 COIL					2112G20020	
R2	6R8	2102C15687				
R1		390R	2102C35391			2X100R IN SERIES 2102C41101
Vdc	24	30	48	60	125	240

- KEY**
- make contact
 - break contact
 - c/o contact
 - ext. conn
 - plug bridge - shorting
 - metering point
 - 5Kv barrier
 - test socket - shorting
 - plug & socket

CONTACT CONFIG.	OUTPUT CONTACT PAIR / TERMINAL No.										
	1-3	2-4	5-7	6-8	9-11	10-12	13-15	14-16	17-19	18-20	
10M	M	M	M	M	M	M	M	M	M	M	M
9M 1B	M	B	M	M	M	M	M	M	M	M	M
8M 2B	B	B	M	M	M	M	M	M	M	M	M
7M 3B	B	B	M	B	M	M	M	M	M	M	M
6M 4B	B	B	B	B	M	M	M	M	M	M	M
5M 5B	B	B	B	B	M	B	M	M	M	M	M
4M 6B	B	B	M	B	M	M	B	B	B	B	M
3M 7B	B	B	B	B	M	M	B	B	B	B	M
2M 8B	B	B	B	B	M	B	B	B	B	B	M

NOTE:

- CONTACT CONFIGURATION ABOVE IS REQUIRED FOR RELAY OPERATION. FOR DETAILS OF VARIABLE CONTACT OPTIONS SEE TABLE OPPOSITE.
- RESISTORS R1 & R2 ARE FITTED ONLY WHEN REQUIRED. SEE TABLE ABOVE.
- DASHED LINE --- SHOWS CONNECTIONS WHEN RESISTORS ARE NOT FITTED.

FRAME REFERENCE: E4FS05.
FRAME TERMINAL BLOCK ASSY: -

ASSEMBLY INSTRUCTIONS: -
TYPICAL ASSEMBLY DRAWING 2995G10032.
AT INDICATED POSITIONS FIT AS FOLLOWS:
T - FIT TRIP ISOLATION CONTACT 2995B10053
S - FIT STANDARD CONTACT 2995B10054
SECURE CONTACTS USING FIXING SCREW 2109F99009.
POSITIONS SHOWN BLANK ARE UNUSED

2	T	T	1
4	T	T	3
6	T	T	5
8	T	T	7
10	T	T	9
12	T	T	11
14	T	T	13
16	T	T	15
18	T	T	17
20	T	T	19
22			21
24			23
26	S	S	25
28	S	S	27

VIEW FROM NUMBERED SIDE OF BLOCK

OUTER TERMINAL BLOCK ASSY: -

ASSEMBLY INSTRUCTIONS: -
TYPICAL ASSEMBLY DRAWING 2995G10029.
AT INDICATED POSITIONS FIT AS FOLLOWS:
S - FIT STANDARD CONTACT 2995B10051
HC - FIT 'HEAVY CURRENT' KIT 2995G10030
WHERE IS SHOWN FIT CT SHORTING KIT 2995G10031
POSITIONS SHOWN BLANK ARE UNUSED.
ALL POSITIONS FIT SCREW 2106F12506.

2	S	S	1
4	S	S	3
6	S	S	5
8	S	S	7
10	S	S	9
12	S	S	11
14	S	S	13
16	S	S	15
18	S	S	17
20	S	S	19
22			21
24			23
26	S	S	25
28	S	S	27

VIEW FROM INSIDE FACE

Title: T.B. AND WIRING DIAG. FOR 7PG15233 (TR233) AND 7PG15243 (TR243) 10 CONTACT RELAYS E4 CASE			First used on:		
6 N.C. 03/06/16 322000105 I.D.			Similar Articles:		
5 RDW 12/04/12 MN112/3514 JB			Supersedes:		
4 07/12/09 MN112/3223			Drg.No.		
ISSUE DATE MOD.No.			Original Scale:		
SIEMENS PROTECTION DEVICES LTD.			2112W50042		
DRAWN: A.LAW.	CHECKED: RD.WATSON	APPROVED: RD.WATSON	DATE: 08/12/2009	IE:	OPS: