

6

Accessories for 8WA and 8WH

8WA accessories

6/2

6/3

6/5

6/5

8WA labeling accessories

- Blank labeling plates
- Inscribed labeling plates
- Other labeling plate accessories
- Other labeling accessories

8WA mounting accessories

6/6

6/6

6/6

6/6

6/6

6/6

6/6

6/7

6/7

6/7

6/7

6/7

- End retainers
- Standard mounting rails
- Test plugs
- Test sockets
- Reduction plugs
- Spacer brackets
- Spacers
- Fastening accessories
- Mounting brackets
- Insulation carriers
- Labeling plates
- Screwdrivers

8WH accessories

6/8

6/9

8WH labeling accessories

- Blank labeling plates
- Inscribed labeling plates

8WH mounting accessories

6/14

6/14

6/14

6/14

6/14

6/15

6/15

6/15

6/15

6/16

6/16

6/16

- Quick-fit end retainers
- Terminal strip markers
- Test adapters
- Lateral mounting test plugs
- Spacer plates
- Connecting combs
- Reducing combs
- Through-type connectors
- Component connectors
- Fused connectors
- Isolating plugs
- Screwdrivers





ALPHA FIX Terminal Blocks

Accessories for 8WA and 8WH

8WA labeling accessories






Selection and ordering data

Version	Order No.	Price	PG	PS* P. unit
		1 unit		Unit(s)
Blank labeling plates				
Labeling plates, for manual inscription				
Not suitable for plotting				
Versions				
<ul style="list-style-type: none"> Label size 5 mm x 7 mm Label size 5 mm x 10 mm 	8WA8 848-2AY 8WA8 800-2AY		041	100
			041	100
Labeling plates, for plotter inscription				
Versions				
 <ul style="list-style-type: none"> For 8WA1 and 8WA2, individually removable <ul style="list-style-type: none"> 5 x 7, white 5 x 10, white Not for two-tier terminals (bottom level); flat-type terminals: 8WA1 010-1PQ00, 8WA1 808 Use individually for 8WA1, or together in grid for 8WA2, terminal size 2.5 mm² <ul style="list-style-type: none"> 5 x 7 5 x 10 For 8WA2 from terminal size 4 mm² <ul style="list-style-type: none"> 6 x 7 6 x 10 	8WA8 850-2AY 8WA8 851-2AY 8WA8 852-2AY 8WA8 854-2AY 8WA8 853-2AY 8WA8 855-2AY		041	1020
			041	1020
			041	1260
			041	1260
			041	1080
			041	1080
Labeling plates, for individual wires				
Versions				
<ul style="list-style-type: none"> 4 x 12, white 4 x 18, white 	Obtainable from: Murrplastik Systems Inc. North American Operations 2367 North Penn Road, Suite 200 Hatfield, PA 19440 Telephone: 877-340-3444 Fax: 215-822-7626 E-mail: cablemgmt@murrplastik.com Internet: www.murrplastik.com			
Device labeling plates				
<ul style="list-style-type: none"> 20 x 9, white 				
	3TX4 210-0R		101	380
Computer labeling system				
for individual inscription of:				
<ul style="list-style-type: none"> Labeling plates for terminal blocks Device labeling plates Labeling plates for individual wires 				
Obtainable from: Murrplastik Systems Inc. North American Operations 2367 North Penn Road, Suite 200 Hatfield, PA 19440 Telephone: 877-340-3444 Fax: 215-822-7626 E-mail: cablemgmt@murrplastik.com Internet: www.murrplastik.com				

ALPHA FIX Terminal Blocks

Accessories for 8WA and 8WH

8WA labeling accessories

Version	Order No.	Price 1 unit	PG	PS* P. unit Unit(s)
Labeling plates, customized inscriptions				
<ul style="list-style-type: none"> Label size 5 mm x 7 mm Character height 2 mm Grid size: 6.2 mm Specify required inscription in plain text 				
Versions				
<ul style="list-style-type: none"> Vertical inscription Horizontal inscription 	8WA8 847-0XA 8WA8 848-0XA		041 041	100 100
Other labeling plate accessories				
	End labeling plates	8WA1 806	041	50
	<ul style="list-style-type: none"> 21 x 42 mm Paper label, inscription possible, with transparent cover Suitable for 8WA1 805, 8WA1 808 and 8WA2 808 end retainers 			
	Group labels	8WA2 838	041	50
	<ul style="list-style-type: none"> White For 8WA2 terminals for plugging onto retaining plates or insulation plates L = 100 mm 			
	Labeling plates, for wires	8WA8 846-2AY	041	1000
	<ul style="list-style-type: none"> Wires from Ø 2 mm to Ø 10 mm Blank labeling plate for inscription with water-proof pen Inscription area 9 mm x 30 mm 			
	Terminal strip labels			
	Suitable for 8WA1 808 and 8WA2 808 end retainers			
Versions				
8WA8 826-0AA	<ul style="list-style-type: none"> Printed with "X1" Printed with "X2" Printed with "X3" Blank 	8WA8 826-0AA 8WA8 826-0AB 8WA8 826-0AC 3TX4 210-0H	041 041 041 101	100 100 100 100
Other labeling accessories				
	Label holders	8WA2 850	041	50
8WA2 850	<ul style="list-style-type: none"> For 8WA2 terminals for insertion into test opening 			










6

ALPHA FIX Terminal Blocks

Accessories for 8WA and 8WH

8WA mounting accessories





Selection and ordering data

Version	Order No.	Price 1 unit	PG	PS* P. unit Unit(s)
 <p>8WA2 808</p> <p>End retainers</p> <ul style="list-style-type: none"> • Light gray • Mounting width 9 mm • Terminal height 31 mm • Terminal length 67mm • Suitable for <ul style="list-style-type: none"> - 8WA1 806 end labeling plate or - 8WA8 826-0A terminal strip labeling plate or - -0H device labeling plate or - 4 8WA8 ... labeling plates • Can also be used for neutral busbar 10 × 3 mm as retainer with the corresponding 8WA2 837 part 	8WA2 808		041	50
 <p>8WA1 808</p> <p>End retainers, with screw fixing</p> <ul style="list-style-type: none"> • Mounting width 10 mm • Suitable for 8WA1 806 end labeling plate or 8WA8 826-0A terminal strip labeling plate or 3TX4 210-0H device labeling plate or four 8WA8 labeling plates. 	8WA1 808		041	50
 <p>8WA1 805</p> <p>End retainers, steel</p> <ul style="list-style-type: none"> • Mounting width 10.3 mm • Suitable for 8WA1 806 end labeling plate <p>Note</p> <p>In the case of an end retainer against the 8WA1 89. link rail (size 2.5) a 8WA1 820 barrier must be inserted.</p>	8WA1 805		041	50
 <p>5ST1 141</p> <p>Standard mounting rails</p> <ul style="list-style-type: none"> • Perforated <ul style="list-style-type: none"> - EN 50022-35 × 7.5 - 2 m long, 1 mm thick, - Steel, Sendzimir galvanized • Without apertures • Non-perforated, copper <ul style="list-style-type: none"> - EN 50022-35 × 15 - 2 m long, 2.3 mm thick, • Non-perforated, steel, galvanized, chromized <ul style="list-style-type: none"> - Similar to EN 50022-35 × 15 - 2 m long, 1.5 mm thick, 	5ST1 145 5ST1 141 8WA7 551 5ST1 142		027	20 027 041 027
 <p>8WA1 867</p> <p>Test plugs</p> <ul style="list-style-type: none"> • For 8WA1 and 8WA2 terminals with 2.3 mm Ø hole or 8WA1 854, 8WA1 884 test sockets • Uninterrupted current 10 A <p>Versions</p> <ul style="list-style-type: none"> • Red 	8WA1 868		041	10
 <p>8WA1 884</p> <p>Test sockets</p> <ul style="list-style-type: none"> • Ø 2, 3 mm • With associated spacer sleeve for link rails, terminal sizes 2.5 and 4 mm², two-tier terminals, rear level, terminal size 6 mm² • Uninterrupted current 10 A <p>Versions</p> <ul style="list-style-type: none"> • Test socket • Space sleeve <p>Note</p> <p>The test socket must be used with a distance sleeve.</p>	8WA1 884 8WA1 822-7VH11		041 041	100 100
 <p>8WA1 871</p> <p>Reduction plugs</p> <ul style="list-style-type: none"> • For 8WA1 and 8WA2 terminals with 2.3 mm Ø hole or 8WA1 854, 8WA1 884 test sockets • Uninterrupted current 10 A • With 4 mm Ø hole 	8WA1 871		041	10
 <p>8WA7 53</p> <p>Spacer brackets</p> <ul style="list-style-type: none"> • For raised mounting of terminal strips 	8WA7 53		041	50
 <p>8WA7 52</p> <p>Spacers</p> <ul style="list-style-type: none"> • With 5.5 mm hole • For raised mounting of terminal strips 	8WA7 52		041	100

ALPHA FIX Terminal Blocks

Accessories for 8WA and 8WH

8WA mounting accessories

Version	Order No.	Price	PG	PS* P. unit
 <p>Fastening accessory for screw mounting of 8WA1 304, 8WA1 011-3DF21, 8WA1 011-3DG21, 8WA1 011-0DG22, 8WA1 011-3DH21 terminal blocks and single terminals (no end retainer required)</p> <p>8WA1 815</p>	8WA1 815	1 unit	041	1 Unit(s)
 <p>Mounting brackets for standard mounting rails</p> <p>8WA7 46</p>	8WA7 46		041	10
 <p>Insulation carriers for insulated mounting of mounting rails onto plates, frame profiles and standard mounting rails EN 50022-35</p> <p>8WA1 857</p>	8WA1 857		041	20
<p>Labeling plates, for identification of insulation carrier</p> <p>8WA1 864</p>	8WA1 864		041	100
 <p>8WA2 803</p> <p>Screwdrivers</p> <ul style="list-style-type: none"> • Green • Approx. 175 mm long <p>Versions</p> <ul style="list-style-type: none"> • Up to terminal size 6 mm² - 3.5 mm × 0.5 mm - 3.5 mm × 0.5 mm, partially insulated 	8WA2 803 8WA2 880		041 041	1 1





6

ALPHA FIX Terminal Blocks

Accessories for 8WA and 8WH

8WH labeling accessories
Inscribed labeling plates



Selection and ordering data

Version	Order No.	Price	PG	PS* P. unit
		1 unit		Unit(s)
Terminal width 4.2 mm				
 8WH8 120-1AB05	Labeling plates, front, for terminal width 4.2 mm, horizontal inscription • Incremental numbering - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) - 41 to 50 (10x) - 51 to 60 (10x) - 61 to 70 (10x) - 71 to 80 (10x) - 81 to 90 (10x) - 91 to 100 (10x) • Custom inscription	8WH8 120-1AB05 8WH8 120-1AB15 8WH8 120-1AB25 8WH8 120-1AB35 8WH8 120-1AB45 8WH8 120-1AB55 8WH8 120-1AB65 8WH8 120-1AB75 8WH8 120-1AB85 8WH8 120-1AC05 8WH8 120-1XA05	044 044 044 044 044 044 044 044 044 044 044 044	100 100 100 100 100 100 100 100 100 100 100 100
 8WH8 140-1AB05	Labeling plates, front, for terminal width 4.2 mm, vertical inscription • Incremental numbering - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) - 41 to 50 (10x) - 51 to 60 (10x) - 61 to 70 (10x) - 71 to 80 (10x) - 81 to 90 (10x) - 91 to 100 (10x) • Custom inscription	8WH8 140-1AB05 8WH8 140-1AB15 8WH8 140-1AB25 8WH8 140-1AB35 8WH8 140-1AB45 8WH8 140-1AB55 8WH8 140-1AB65 8WH8 140-1AB75 8WH8 140-1AB85 8WH8 140-1AC05 8WH8 140-1XA05	044 044 044 044 044 044 044 044 044 044 044 044	100 100 100 100 100 100 100 100 100 100 100 100
 8WH8 110-1AA05	Labeling plates, front, for terminal width 4.2 mm, blank	8WH8 110-1AA05	044	100
 8WH8 121-1AB05	Labeling plates, flat, for terminal width 4.2 mm, horizontal inscription • Incremental numbering - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) - 41 to 50 (10x) - 51 to 60 (10x) - 61 to 70 (10x) - 71 to 80 (10x) - 81 to 90 (10x) - 91 to 100 (10x) • Custom inscription	8WH8 121-1AB05 8WH8 121-1AB15 8WH8 121-1AB25 8WH8 121-1AB35 8WH8 121-1AB45 8WH8 121-1AB55 8WH8 121-1AB65 8WH8 121-1AB75 8WH8 121-1AB85 8WH8 121-1AC05 8WH8 121-1XA05	044 044 044 044 044 044 044 044 044 044 044	100 100 100 100 100 100 100 100 100 100 100
 8WH8 141-1AB05	Labeling plates, flat, for terminal width 4.2 mm, vertical inscription • Incremental numbering - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) - 41 to 50 (10x) - 51 to 60 (10x) - 61 to 70 (10x) - 71 to 80 (10x) - 81 to 90 (10x) - 91 to 100 (10x) • Custom inscription	8WH8 141-1AB05 8WH8 141-1AB15 8WH8 141-1AB25 8WH8 141-1AB35 8WH8 141-1AB45 8WH8 141-1AB55 8WH8 141-1AB65 8WH8 141-1AB75 8WH8 141-1AB85 8WH8 141-1AC05 8WH8 141-1XA05	044 044 044 044 044 044 044 044 044 044 044	100 100 100 100 100 100 100 100 100 100 100
 8WH8 111-1AA05	Labeling plates, flat, for terminal width 4.2 mm, blank	8WH8 111-1AA05	044	100

ALPHA FIX Terminal Blocks

Accessories for 8WA and 8WH








8WH labeling accessories Inscribed labeling plates

Version	Order No.	Price 1 unit	PG	PS* P. unit Unit(s)
Terminal width 5.2 mm				
 8WH8 120-2AB05	Labeling plates, front, for terminal width 5.2 mm, horizontal inscription <ul style="list-style-type: none"> Incremental numbering <ul style="list-style-type: none"> - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) - 41 to 50 (10x) - 51 to 60 (10x) - 61 to 70 (10x) - 71 to 80 (10x) - 81 to 90 (10x) - 91 to 100 (10x) L1/L2/L3/N/PE Custom inscription 	8WH8 120-2AB05 8WH8 120-2AB15 8WH8 120-2AB25 8WH8 120-2AB35 8WH8 120-2AB45 8WH8 120-2AB55 8WH8 120-2AB65 8WH8 120-2AB75 8WH8 120-2AB85 8WH8 120-2AC05 8WH8 120-2AA15 8WH8 120-2XA05	044 044 044 044 044 044 044 044 044 044 044 044 044	100 100 100 100 100 100 100 100 100 100 100 100 100
 8WH8 120-2AA15	Labeling plates, front, for terminal width 5.2 mm, vertical inscription <ul style="list-style-type: none"> Incremental numbering <ul style="list-style-type: none"> - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) - 41 to 50 (10x) - 51 to 60 (10x) - 61 to 70 (10x) - 71 to 80 (10x) - 81 to 90 (10x) - 91 to 100 (10x) Custom inscription 	8WH8 140-2AB05 8WH8 140-2AB15 8WH8 140-2AB25 8WH8 140-2AB35 8WH8 140-2AB45 8WH8 140-2AB55 8WH8 140-2AB65 8WH8 140-2AB75 8WH8 140-2AB85 8WH8 140-2AC05 8WH8 140-2XA05	044 044 044 044 044 044 044 044 044 044 044 044 044	100 100 100 100 100 100 100 100 100 100 100 100 100
 8WH8 110-2AA05	Labeling plates, front, for terminal width 5.2 mm, blank	8WH8 110-2AA05	044	100
 8WH8 121-2AB05	Labeling plates, flat, for terminal width 5.2 mm, horizontal inscription <ul style="list-style-type: none"> Incremental numbering <ul style="list-style-type: none"> - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) - 41 to 50 (10x) - 51 to 60 (10x) - 61 to 70 (10x) - 71 to 80 (10x) - 81 to 90 (10x) - 91 to 100 (10x) Custom inscription 	8WH8 121-2AB05 8WH8 121-2AB15 8WH8 121-2AB25 8WH8 121-2AB35 8WH8 121-2AB45 8WH8 121-2AB55 8WH8 121-2AB65 8WH8 121-2AB75 8WH8 121-2AB85 8WH8 121-2AC05 8WH8 121-2XA05	044 044 044 044 044 044 044 044 044 044 044 044 044	100 100 100 100 100 100 100 100 100 100 100 100 100
 8WH8 141-2AB05	Labeling plates, flat, for terminal width 5.2 mm, vertical inscription <ul style="list-style-type: none"> Incremental numbering <ul style="list-style-type: none"> - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) - 41 to 50 (10x) - 51 to 60 (10x) - 61 to 70 (10x) - 71 to 80 (10x) - 81 to 90 (10x) - 91 to 100 (10x) Custom inscription 	8WH8 141-2AB05 8WH8 141-2AB15 8WH8 141-2AB25 8WH8 141-2AB35 8WH8 141-2AB45 8WH8 141-2AB55 8WH8 141-2AB65 8WH8 141-2AB75 8WH8 141-2AB85 8WH8 141-2AC05 8WH8 141-2XA05	044 044 044 044 044 044 044 044 044 044 044 044 044	100 100 100 100 100 100 100 100 100 100 100 100 100
 8WH8 111-2AA05	Labeling plates, flat, for terminal width 5.2 mm, blank	8WH8 111-2AA05	044	100

ALPHA FIX Terminal Blocks

Accessories for 8WA and 8WH











8WH labeling accessories Inscribed labeling plates

Version	Order No.	Price 1 unit	PG	PS* P. unit Unit(s)
Terminal width 8.2 mm				
 8WH8 120-4AB05  8WH8 120-4AA15	Labeling plates, front, for terminal width 8.2 mm, horizontal inscription <ul style="list-style-type: none"> Incremental numbering <ul style="list-style-type: none"> - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) - 41 to 50 (10x) - 51 to 60 (10x) - 61 to 70 (10x) - 71 to 80 (10x) - 81 to 90 (10x) - 91 to 100 (10x) L1/L2/L3/N/PE Custom inscription 	8WH8 120-4AB05 8WH8 120-4AB15 8WH8 120-4AB25 8WH8 120-4AB35 8WH8 120-4AB45 8WH8 120-4AB55 8WH8 120-4AB65 8WH8 120-4AB75 8WH8 120-4AB85 8WH8 120-4AC05 8WH8 120-4AA15 8WH8 120-4XA05	044 044 044 044 044 044 044 044 044 044 044 044 044 044	100 100 100 100 100 100 100 100 100 100 100 100 100 100
 8WH8 140-4AB05	Labeling plates, front, for terminal width 8.2 mm, vertical inscription <ul style="list-style-type: none"> Incremental numbering <ul style="list-style-type: none"> - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) - 41 to 50 (10x) - 51 to 60 (10x) - 61 to 70 (10x) - 71 to 80 (10x) - 81 to 90 (10x) - 91 to 100 (10x) Custom inscription 	8WH8 140-4AB05 8WH8 140-4AB15 8WH8 140-4AB25 8WH8 140-4AB35 8WH8 140-4AB45 8WH8 140-4AB55 8WH8 140-4AB65 8WH8 140-4AB75 8WH8 140-4AB85 8WH8 140-4AC05 8WH8 140-4XA05	044 044 044 044 044 044 044 044 044 044 044 044	100 100 100 100 100 100 100 100 100 100 100 100
 8WH8 110-4AA05	Labeling plates, front, for terminal width 8.2 mm, blank	8WH8 110-4AA05	044	100
 8WH8 121-4AB05	Labeling plates, flat, for terminal width 8.2 mm, horizontal inscription <ul style="list-style-type: none"> Incremental numbering <ul style="list-style-type: none"> - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) - 41 to 50 (10x) - 51 to 60 (10x) - 61 to 70 (10x) - 71 to 80 (10x) - 81 to 90 (10x) - 91 to 100 (10x) Custom inscription 	8WH8 121-4AB05 8WH8 121-4AB15 8WH8 121-4AB25 8WH8 121-4AB35 8WH8 121-4AB45 8WH8 121-4AB55 8WH8 121-4AB65 8WH8 121-4AB75 8WH8 121-4AB85 8WH8 121-4AC05 8WH8 121-4XA05	044 044 044 044 044 044 044 044 044 044 044 044	100 100 100 100 100 100 100 100 100 100 100 100
 8WH8 141-4AB05	Labeling plates, flat, for terminal width 8.2 mm, vertical inscription <ul style="list-style-type: none"> Incremental numbering <ul style="list-style-type: none"> - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) - 41 to 50 (10x) - 51 to 60 (10x) - 61 to 70 (10x) - 71 to 80 (10x) - 81 to 90 (10x) - 91 to 100 (10x) Custom inscription 	8WH8 141-4AB05 8WH8 141-4AB15 8WH8 141-4AB25 8WH8 141-4AB35 8WH8 141-4AB45 8WH8 141-4AB55 8WH8 141-4AB65 8WH8 141-4AB75 8WH8 141-4AB85 8WH8 141-4AC05 8WH8 141-4XA05	044 044 044 044 044 044 044 044 044 044 044 044	100 100 100 100 100 100 100 100 100 100 100 100
 8WH8 111-3AA05	Labeling plates, flat, for terminal width 8.2 mm, blank	8WH8 111-3AA05	044	100

ALPHA FIX Terminal Blocks

Accessories for 8WA and 8WH

8WH labeling accessories Inscribed labeling plates






Version	Order No.	Price	PG	PS* P. unit
		1 unit		Unit(s)
Terminal width 10 mm				
 8WH8 120-5AB05	Labeling plates, front, for terminal width 10 mm, horizontal inscription • Incremental numbering - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) • L1/L2/L3/N/PE • Custom inscription • U/V/W/N/grounding	8WH8 120-5AB05 8WH8 120-5AB15 8WH8 120-5AB25 8WH8 120-5AB35 8WH8 120-5AA15 8WH8 120-5XA05 8WH8 120-5AA25	044 044 044 044 044 044 044	100 100 100 100 100 100 100
 8WH8 120-5AA15				
 8WH8 120-5AA25				
 8WH8 140-5AB05	Labeling plates, front, for terminal width 10 mm, vertical inscription • Incremental numbering - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) • Custom inscription	8WH8 140-5AB05 8WH8 140-5AB15 8WH8 140-5AB25 8WH8 140-5AB35 8WH8 140-5XA05	044 044 044 044 044	100 100 100 100 100
 8WH8 110-5AA05	Labeling plates, front, for terminal width 10 mm, blank	8WH8 110-5AA05	044	100
 8WH8 121-5AB05	Labeling plates, flat, for terminal width 10 mm, horizontal inscription • Incremental numbering - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) • Custom inscription	8WH8 121-5AB05 8WH8 121-5AB15 8WH8 121-5AB25 8WH8 121-5AB35 8WH8 121-5XA05	044 044 044 044 044	100 100 100 100 100
 8WH8 141-5AB05	Labeling plates, flat, for terminal width 10 mm, vertical inscription • Incremental numbering - 1 to 10 (10x) - 11 to 20 (10x) - 21 to 30 (10x) - 31 to 40 (10x) • Custom inscription	8WH8 141-5AB05 8WH8 141-5AB15 8WH8 141-5AB25 8WH8 141-5AB35 8WH8 141-5XA05	044 044 044 044 044	100 100 100 100 100
 8WH8 111-5AA05	Labeling plates, flat, for terminal width 10 mm, blank	8WH8 111-5AA05	044	100
Terminal width 15 mm				
 8WH8 120-7AA15	Labeling plates, front, for terminal width 15 mm, horizontal inscription • L1/L2/L3/N/PE • Custom inscription	8WH8 120-7AA15 8WH8 120-7XA05	044 044	100 100
	Labeling plates, front, for terminal width 15 mm, vertical custom inscription	8WH8 140-7XA05	044	100
 8WH8 110-7AA05	Labeling plates, front, for terminal width 15 mm, blank	8WH8 110-7AA05	044	100
	Labeling plates, flat, for terminal width 15 mm, blank	8WH8 111-7AA05	044	100

ALPHA FIX Terminal Blocks

Accessories for 8WA and 8WH

8WH mounting accessories





Selection and ordering data

Version	Order No.	Price	PG	PS* P. unit
		1 unit		Unit(s)
 <p>Quick-fit end retainers</p> <ul style="list-style-type: none"> For labeling with front labeling plates, for terminal width 5.2 mm and terminal strip markers 	8WH9 150-0CA00		044	50
8WH9 150-0CA00				
 <p>Terminal strip markers, for end retainers</p> <ul style="list-style-type: none"> Height-adjustable For quick-fit end retainers Inscription possible with terminal strip marker or two labeling plates, front, for terminal width 10.2 mm Labeling field size: 20 x 8 mm 	8WH9 150-1CA00		044	100
8WH9 150-1CA00				
 <p>Test adapters</p> <ul style="list-style-type: none"> For 4 mm Ø PS test plugs and 4 mm Ø safety test plugs Makes contact in the bridge slot 	8WH9 010-0JB00		044	10
8WH9 010-0JB00				
 <p>Lateral mounting test plugs for individual assembly of test plug strips</p> <p>Versions</p> <ul style="list-style-type: none"> For terminal width 4.2 mm For terminal width 5.2 mm For terminal width 6.2 mm For terminal width 8.2 mm 	8WH9 010-0DB02 8WH9 010-0EB02 8WH9 010-0FB02 8WH9 010-0GB02		044	10
8WH9 010-0DB02				
 <p>Spacer plates for skipping single terminals for individual test adapter assembly</p> <p>Versions</p> <ul style="list-style-type: none"> For terminal width 4.2 mm For terminal width 5.2 mm For terminal width 6.2 mm For terminal width 8.2 mm 	8WH9 010-2AA02 8WH9 010-2BA02 8WH9 010-2CA02 8WH9 010-2DA02		044	10
8WH9 010-2AA02				

ALPHA FIX Terminal Blocks

Accessories for 8WA and 8WH





8WH mounting accessories

Version	Order No.	Price	PG	PS* P. unit	
		1 unit		Unit(s)	
 <p>8WH9 020-6AC10</p>	Connecting combs				
	<ul style="list-style-type: none"> • For terminal width 4.2 mm <ul style="list-style-type: none"> - 2-pole - 3-pole - 4-pole - 5-pole - 10-pole - 20-pole 				
		8WH9 020-6AC10		044	50
		8WH9 020-6AD10		044	50
		8WH9 020-6AE10		044	50
		8WH9 020-6AF10		044	50
		8WH9 020-6AL10		044	10
		8WH9 020-6AS10		044	10
		<ul style="list-style-type: none"> • For terminal width 5.2 mm <ul style="list-style-type: none"> - 2-pole - 3-pole - 4-pole - 5-pole - 10-pole - 20-pole - 50-pole 			
		8WH9 020-6BC10		044	50
		8WH9 020-6BD10		044	50
		8WH9 020-6BE10		044	50
		8WH9 020-6BF10		044	50
		8WH9 020-6BL10		044	10
		8WH9 020-6BS10		044	10
		8WH9 020-6BT10		044	10
		<ul style="list-style-type: none"> • For terminal width 6.2 mm <ul style="list-style-type: none"> - 2-pole - 3-pole - 4-pole - 5-pole - 10-pole - 20-pole - 50-pole 			
		8WH9 020-6CC10		044	50
		8WH9 020-6CD10		044	50
		8WH9 020-6CE10		044	50
	8WH9 020-6CF10		044	50	
	8WH9 020-6CL10		044	10	
	8WH9 020-6CS10		044	10	
	8WH9 020-6CT10		044	10	
	<ul style="list-style-type: none"> • For terminal width 8.2 mm <ul style="list-style-type: none"> - 2-pole - 3-pole - 4-pole - 5-pole - 10-pole 				
	8WH9 020-6DC10		044	10	
	8WH9 020-6DD10		044	10	
	8WH9 020-6DE10		044	10	
	8WH9 020-6DF10		044	10	
	8WH9 020-6DL10		044	10	
	<ul style="list-style-type: none"> • For terminal width 10 mm, 2-pole • For terminal width 12 mm, 2-pole • For terminal width 16 mm, 2-pole 				
	8WH9 020-6EC10		044	10	
	8WH9 020-6FC10		044	10	
	8WH9 020-6GC10		044	10	
 <p>8WH9 020-0FC10</p>	Reducing combs				
	<ul style="list-style-type: none"> • For connecting to a through-type terminal, terminal size 2.5 or 4 mm² <ul style="list-style-type: none"> - To a through-type terminal, terminal size 6 mm², I_{max}: 48 A - To a through-type terminal, terminal size 10 mm², I_{max}: 55 A - To a through-type terminal, terminal size 16 mm², I_{max}: 64 A - To a through-type terminal, terminal size 35 mm², I_{max}: 64 A • For connecting to a through-type terminal, terminal size 16 mm² <ul style="list-style-type: none"> - To a through-type terminal, terminal size 35 mm², I_{max}: 90 A 				
		8WH9 020-0FC10		044	10
		8WH9 020-0AC10		044	10
		8WH9 020-0BC10		044	10
		8WH9 020-0EC10		044	10
	8WH9 020-0DC10		044	10	
 <p>8WH9 020-8AB00</p>	Through-type connectors				
	<ul style="list-style-type: none"> • Gray • I_{max}: 16 A 				
	8WH9 020-8AB00		044	50	
 <p>8WH9 040-0BB00</p>	Component connectors				
	<ul style="list-style-type: none"> • I_{max}: 6 A, depending on the power loss of the components, max. 1 W with single arrangement • Inscription possible with labeling plates, flat, for terminal width 5.2 mm 				
	8WH9 040-0BB00		044	10	

ALPHA FIX Terminal Blocks

Accessories for 8WA and 8WH

8WH mounting accessories

Version	Order No.	Price	PG	PS* P. unit		
		1 unit		Unit(s)		
 <p>8WH9 040-3AB08</p>	Fused connectors					
	<ul style="list-style-type: none"> • Black • I_{max}: 6,3 A • Inscription possible with labeling plates, flat, for terminal width 5,2 mm 					
	Versions					
	<ul style="list-style-type: none"> • With LED display for 12 to 30 V • With LED display for 30 to 60 V • With LED display for 110 to 250 V • Without LED display 		<ul style="list-style-type: none"> 1 ... 2,5 mA 0,8 ... 2,0 mA 0,5 ... 2,5 mA 	<ul style="list-style-type: none"> 8WH9 040-3AB08 8WH9 040-3BB08 8WH9 040-3CB08 8WH9 040-3DB08 	<ul style="list-style-type: none"> 044 044 044 044 	<ul style="list-style-type: none"> 10 10 10 10
	Note					
<p>Select G fuse holders according to the max. power loss (heat dissipation) of the G fuse links. Test the heating conditions in enclosed fuse holders, which depend on application and installation method.</p> <p>Higher ambient temperatures present an additional burden for the fuse links. In this case, take the offset of the rated current into account.</p>						
 <p>8WH9 040-3DB08</p>						
 <p>8WH9 040-0DB04</p>	Isolating plugs					
	<ul style="list-style-type: none"> • Orange 					
 <p>8WH9 200-0AA00</p>	Screwdrivers					
	for actuating the tension springs					
	Versions					
	<ul style="list-style-type: none"> • 0,4 x 2,5 mm • 0,4 x 3,5 mm • 0,8 x 4,0 mm • 1,0 x 5,5 mm 		<ul style="list-style-type: none"> 8WH9 200-0AA00 8WH9 200-0AB00 8WH9 200-0AC00 8WH9 200-0AD00 	<ul style="list-style-type: none"> 044 044 044 044 	<ul style="list-style-type: none"> 10 10 10 10 	