



**SIEMENS**

*Ingenuity for life*

## Vectron Dual Mode

Keeps going where the wire ends

Whenever an overhead wire is available, it should be used. Electrical operation is much more cost-effective and environmentally friendly than diesel operation. But because Germany will continue to have many non-electrified sections of track for a long time to come, many diesel locomotives continue to operate under a contact line. This makes very little economic or ecological sense. What if there were a real alternative – a locomotive that excels at both operating modes?

### **When subsections become a unified whole**

Vectron® Dual Mode adapts itself to the route. With powerful diesel traction as well as equipment for using the overhead wire, you're free to change at any time. You can operate extremely efficiently and economically under catenary for long sections of track. When necessary, just switch over – and keep moving, whatever the conditions.













Longer subsections without an overhead wire, unplanned detours, the reduction of fine particulates in metropolitan areas: There are many reasons to opt for flexible traction. Vectron Dual Mode combines the benefits of a full-featured diesel locomotive with those of an electric locomotive, with verifiably profitable results. So drive ahead!

# When savings open up new paths

By choosing Vectron Dual Mode today, you're opting for proven technology that you can continue to rely on tomorrow and beyond – while also enjoying maximum flexibility, saving money, and protecting the environment. You benefit from extreme availability and planning reliability, even when conditions change.




### Components

- |  |  |  |
|--|--|--|
|  Dynamic braking resistor |  Particle filter  |  Brake rack       |
|  Train-protection cabinet |  Engine air intake system                                     |  Fuel tank        |
|  Engine cooling plant     |  Alternator   |  Main transformer |
|  Diesel engine            |  Electric cabinet with central blower and switching equipment |  Pantograph       |

### Drastically reduce costs

With Vectron Dual Mode, running on electricity alone when on electrified track sections is a matter of course. Every kilometer saves fuel and thus reduces energy costs. You also reduce the number of hours your diesel generator set is operating, which in turn decreases maintenance outlay. Consequently, Vectron Dual Mode handles a wide range of traction tasks much more economically than a standard diesel locomotive. So why not use electric power when it's available?

## Example application: Vectron Dual Mode compared to pure diesel operation\*



\*with an average annual mileage of 150,000 kilometers and 4,000 operating hours per freight locomotive



### Improve environmental performance

Vectron Dual Mode protects the environment. It enables you to make an important contribution and cut down on emissions – factors that are becoming increasingly important in cities and metropolitan areas. By taking advantage of electricity wherever possible, you demonstrably reduce carbon dioxide, nitrogen oxide, and particulate matter emissions, thereby improving your fleet's environmental performance.

### Technical data

Diesel engine power (at the crankshaft)	2,400 kW As per UIC 623-2:2010	Vehicle length (length over buffers)	19,975 mm
Voltage system	15 kV/16.7 Hz	Track gauge	1,435 mm
Starting tractive effort	300 kN	Fuel tank volume (usable)	2,500 l
Traction power at the wheel rim	2,000 kW	Wheel diameter	1,100 mm new / 1,020 mm worn
Electric braking effort	150 kN	Weight (max.)	90 t when fully loaded
Electric braking power at the wheel rim	E-mode: 2,100 kW Diesel mode: 1,700 kW	Double traction	Via WTB ÖBB: with same-type vehicles as well as Vectron E, Vectron DE, and ER20
Max. speed	160 km/h	Train protection	PZB, ready for ETCS
Wheelset arrangement	Bo'Bo'	Axle load	22.5 t
Area of application	Freight transport		



**Published by  
Siemens Mobility GmbH 2018**

Siemens Mobility GmbH  
Otto-Hahn-Ring 6  
81739 Munich, Germany

[locomotives.mobility@siemens.com](mailto:locomotives.mobility@siemens.com)

Order No. MOML-B10057-00-7600  
Printed in Germany  
Dispo 21715  
HL 18053751 WS 08180.5

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.

Vectron® is a registered trademark of Siemens Mobility GmbH.