

7SV512 numerical circuit-breaker failure protection relay




Fig. 1
7SV512 numerical circuit-breaker failure protection relay

Application

The 7SV512 is a numerical relay used for circuit-breaker failure protection. This condition is when the circuit-breaker fails to correctly open and clear the fault after single- or three-pole trip commands have been issued by the protection. It is then necessary to trip the relevant busbar zone (section) to ensure fault clearance. Generally, the monitoring of the current suffices as the criteria for the indication that the circuit-breaker has successfully cleared the fault ("current condition"). However, under certain fault conditions, (e.g. overvoltage) little or no current may flow making the measurement of current unreliable for indication of the circuit-breaker status ("no current condition"). The 7SV512 will operate correctly for both these conditions. The high security of the relay (against overfunction) is achieved with a unique microprocessor independent "trip release function" in conjunction with a fast current reset time and a 2-out-of-4 current measurement check. An independent pole discrepancy protection is included. The relay is suitable for use at all voltage levels and in all applications. The current transformers can either be of the closed iron core or linear type. The relay can be incorporated in conventional switchgear systems and modern substation control systems e.g. Siemens SINAUT LSA.

Construction

Within its compact construction, the device contains:

- Inputs and circuitry necessary for digitization and evaluation of the current
- Operator keypad with display
- Event (alarm) and trip (command) output contacts
- Binary inputs
- Serial interfaces
- Power supply converter (DC/DC converter)

The device can be supplied in two housing variations. The option for flush mounting or mounting in a cubicle has rear connection terminals. The model for surface mounting is supplied with two-tier terminals accessible from the front.

Implemented functions/features

The following functions are included:

- Circuit-breaker failure protection (single- or three-pole with/without current)
- End fault protection
- Pole discrepancy protection
- Complete relay self monitoring
- Disturbance recording
- Fault and operating data (event records)

- Parameter set changeover facility (4 sets of parameters)
- Display of on-line measured current values
- Real-time clock with non-volatile annunciation memory (option)

With the following features:

- 2-out-of-4 current check
- Phase selective for single- and three-pole operation
- Fast reset time with no overshoot
- Very sensitive current detection
- Independently settable delay times for operation with and without current
- Single or two stage time delay of the busbar trip command
- Microprocessor independent trip release function (hardware interlock)
- Cross trip stage (1st stage of the 2 stage operation)
- Circuit-breaker defective input facilitates a separate busbar trip time delay
- Inter-trip facility (via teleprotection interface)
- End fault protection with inter-trip
- "No current" condition control using the circuit-breaker auxiliary contacts

7SV512 numerical circuit-breaker failure protection relay

Mode of operation

Proven sample and hold techniques, in conjunction with anti-aliasing filters are used, providing a reliable platform for the data acquisition in the 7SV512.

With the use of a powerful microprocessor and digital filtering techniques, the influence of high frequency transients, and DC current components are suppressed. The measured values are calculated using finite impulse response (FIR) filters.

Serial interfaces

The relay is supplied with two serial interfaces.

The RS232 serial interface on the front panel of the relay is suitable for communication with a PC. A software package (DIGSI®) is available for convenient menu-guided parameter setting, relay commissioning, transfer and evaluation of fault operation details, and reading of the fault wave forms stored in the relay.

The system interface, on the rear of the relay, is optionally available as a fibre optic interface for connection to either the substation control system e.g. Siemens SINAUT LSA, or to a central data processing unit.

Settings

All setting parameters can be entered via the integrated operator keypad or via a PC connected to the front serial interface of the relay. The settings and marshalling are stored in a non-volatile memory, and are thus secured against interruption/loss of the DC supply voltage.

Self monitoring

Extensive hardware and software monitoring functions are integrated in the 7SV512. Any irregularities in the hardware or software are immediately detected and alarmed. As a result, the security, reliability and availability of the protection relay are significantly improved.

The monitoring functions include:

- Hardware monitoring with:
 - monitoring of the analog to digital (A to D) converters
 - command / trip relay supervision
 - monitoring of the memory modules
- Software monitoring with extensive routines and watchdog functions
- Current symmetry supervision
- Current summation supervision

Circuit-breaker failure protection

The circuit-breaker failure protection is the main function in the 7SV512. The circuit-breaker failure function is phase selectively processed. The initiation is via the binary inputs connected to the protection. When a valid initiation is received and current is flowing:

1. Above the current set value ("current condition"), the relay measures the time taken for the current to drop below this set value. If this time exceeds a settable time (T1) it will issue a local trip command (cross trip) to re-trip its own circuit-breaker. If this is unsuccessful and a second timer (T2 current) times out, before the current drops below the set value, it will issue a busbar trip command. The current measurement is only valid when current in at least 2-out-of-4 of the current inputs is above the set value. The plausibility check with single phase faults can be done either, with measured residual (earth) current, or with the calculated negative sequence current.
2. Below the current set value, the relay if required, switches over to the "no current condition" and operates with the connected circuit-breaker auxiliary contacts. The sequence is then as described above. A separate busbar trip time delay (T2, no current) can be set for this condition.

Once the relay has been initiated, for example with a "current condition", then this condition is maintained until the fault detection input resets.

An initiation input is only taken as valid when both the fault detection input and the trip input are present (i.e. 2-out-of-2). A false initiation is thus prevented.

Additionally the microprocessor independent "trip release function" (hardware interlock) prevents any incorrect tripping due to possible errors within the microprocessor, when no valid initiation input exists. Fig. 2 gives an overview of this function.

Of great importance in circuit-breaker failure protection is the reset speed of the current detector of the relay, once the circuit-breaker has successfully cleared the fault. The fast current reset of the 7SV512 is ensured, even with a large DC offset, by the versatile digital filtering. Current with a slow decay (long time constant) is therefore of no consequence, and the current detector will still reset within the specified time.

Should the circuit-breaker be unable to trip, (e.g. due to no hydraulic pressure), the busbar trip command can be issued faster using a separately settable time stage. This time stage is enabled via a binary input, of the 7SV512, connected to the circuit-breaker mechanism.

If one of the relay supervision functions (e.g. current summation or hardware monitoring) picks up, the circuit-breaker failure protection can, if necessary, be blocked after a settable duration.

With all the above mentioned security checks and interlocks a high degree of safety against maloperation is achieved with this critical protection function.

End fault protection

This function is required for cases where a fault occurs between the circuit-breaker and the current transformer once the circuit-breaker is open. An independently settable time delay is started after a valid initiation is received and the circuit-breaker auxiliary contacts indicate that the circuit-breaker has opened, but current is still flowing. After the expiry of this time delay an inter-trip signal is given to the remote end.

Pole discrepancy protection

This function ensures that any one or two poles of a circuit-breaker do not remain open for longer than an independently settable time (i.e. unsymmetrical conditions). This time stage is initiated when current (above the set value) is flowing in any 1 or 2 phases, but not in all 3 phases. Additionally, the circuit-breaker auxiliary contacts (if connected) are interrogated and must show the same condition as the current measurement. Should this time delay expire, then a three pole trip command is issued. This function is normally used when single pole auto-reclosing is practiced.

Parameter set changeover

With the help of a binary input, the integrated operator panel or with DIGSI, 1 of the 4 completely separate sets of parameter settings can be activated. This facility enables, for example, matching of the relay's parameter settings to the changing of the network configuration.

Display of in-service measured values

The 7SV512 can display the line currents I_{L1} , I_{L2} , I_{L3} and I_E .

7SV512 numerical circuit-breaker failure protection relay

Fault reports

The relay stores event lists (operational records) and fault reports. All the following alarms in memory are protected against loss of the auxiliary supply, when the option with the real-time clock and non-volatile annunciation memory is selected. (When this option is not selected then the following are lost when the auxiliary supply is removed.)

- **Fault report**
The fault reports of the last three disturbances are always available from the relay
- **Operational reports**
All annunciations which do not belong to the fault reports are saved in the operational reports
- **Switching statistics**
The number of single- and three-pole trips, as well as the sum of currents interrupted in each phase can be read out
- **Automatic information display**
When selected, two operational measured values can be displayed on the liquid crystal display (LCD). These values are continuously updated by the relay. After a fault, two sets of fault data can be automatically displayed on the LCD. The user can select which data should be displayed.

Real-time clock (option)

The internal clock with battery back-up is available as an option. The clock can be synchronized with the integrated operator panel, or with DIGSI® by using a binary input. All alarms are time and date stamped. When this option is not selected then time stamps are in relative time.

Disturbance recording

Digital measured values of phase and earth currents are stored, starting 100 ms (83 ms in 60 Hz systems) before fault detection until the end of the fault, or a max. of 3 seconds (2.5 seconds in 60 Hz systems) of fault buffer has been filled. The fault data has a 1 ms (0.83 ms in 60 Hz systems) time resolution.

Time markers for specific relay reactions, such as general fault detection, trip, and reset, help analyzing disturbances on the system. A disturbance recording stored in the relay will be overwritten by a new fault occurrence. Therefore the most recent fault is always stored in the relay. The disturbance data can be transferred to the substation control system, e.g. Siemens SINAUT LSA, or to a PC for evaluation.

Marshalling of command and alarm/event relays, LEDs and binary inputs

The relay is supplied with a number of command (trip) and event (alarm) output relays, binary inputs and LEDs.

For user specific alarms, flags and trips, all command relays, alarm relays and LEDs are freely marshallable. The only constraint is that if the trip release function (hardware interlock) is required then the binary inputs 8, 9, and 10 must be used (see Fig. 2). A number of annunciations can be grouped together to create a special (group) annunciation for flags, alarms and trips. The LEDs can be allocated for self reset or to get latched until they are manually reset. In the event of loss of the auxiliary power supply, the flags (LEDs) which have not been reset, are again restored with the restoration of the auxiliary power supply. (Only with the option of the real-time clock and non-volatile annunciation memory).

Technical data

Input circuits	Rated current I_N Rated frequency f_N Thermal overload capability in current path continuous for 10 s for 1 s Dynamic overload capability (half cycle) Burden current inputs $I_N = 1 \text{ A}$ $I_N = 5 \text{ A}$	1 A or 5 A 50 Hz or 60 Hz (selectable) $4 \times I_N$ $20 \times I_N$ $100 \times I_N$ $250 \times I_N$ approx. 0.1 VA approx. 0.2 VA
Power supply via integrated DC/DC converter	Rated auxiliary voltage V_{auxH} //(permissible tolerance) Maximum permissible ripple at rated voltage at voltage limit Power consumption quiescent (with 110 V DC) energized Max. bridging time during loss of auxiliary voltage	24 V, 48 V DC (19 V to 56 V) 60 V, 110 V, 125 V DC (48 V to 144 V) 220 V, 250 V DC (176 V to 288 V) $\leq 12 \%$ $\leq 6 \%$ approx. 6.3 W approx. 13.5 W > 50 ms for $V_{auxH} > 110 \text{ V}$
Binary inputs	Number Voltage range (selectable via links) Current consumption (independent of operating voltage)	10 (marshallable) 24 V to 69 V DC and 69 V to 250 V DC approx. 2.5 mA
Alarm/event contacts	Number of relays (total) Contact breakdown number of C/O contacts number of N/O contacts Switching capacity make/break Switching voltage Permissible current continuous	8 (marshallable) each with 1 contact 5 (marshallable) 3 (marshallable) 20 W/VA 250 V AC/DC 1 A

Devices for Various Applications

7SV512 numerical circuit-breaker failure protection relay

Technical data

Command contacts (Trip)	Number of relays, each with 2 N/O contacts Switching capacity make break Switching voltage (max.) Permissible current, continuous 0.5 s	5 (marshallable) 1000 W/VA 30 W/VA 250 V AC/DC 5 A 30 A
LED displays	Ready indication green Blocked indication red Marshallable LEDs red	1 1 6
Serial interfaces	Operator interface Baud rate System interface Baud rate Fibre optic connection optical wavelength permissible attenuation distance	non-isolated, 25-pole D-type sub-miniature front port (ISO 2110) for connection to a PC 1200 Bd to 19200 Bd potential free interface for connection to a central unit 4800 Bd to 19200 Bd integrated FSMA connectors for connection to fibre optic cables 820 nm max. 8 db with glass fibre 62.5/125 µm max. 1.5 km
Construction of unit	Housing flush mounting/cubicle mounting surface mounting Dimensions Weight: flush mounting/cubicle mounting surface mounting Degree of protection according to EN 60 529 Housing Terminals	7XP2030-1 7XP2030-2 approx. 9.5 kg approx. 11 kg IP 51 IP 21
Standards	DIN VDE 0435, Part 303 and IEC 255-5 or IEC 255-6	
Insulation tests	Voltage tests (100% test): V_{aux} DIN VDE 0435 part 303 and IEC 255-5 or IEC 255-6 Impulse voltage tests (100% test) or other circuits DIN VDE 0435 part 303 and IEC 255-5 or IEC 255-6 Impulse voltage tests (type test) DIN VDE 0435 part 303 and IEC 255-5 or IEC 255-6	2.8 kV DC; 30 s per polarity 2 kV (rms), 50 Hz, 1 min 5 kV (peak); 1.2/50 µs; 0.5 J; 3 positive and 3 negative shots at intervals of 5 s
Disturbance tests	High frequency test (1 MHz test) IEC255-22-1, Class III Electrostatic discharge test (ESD test) IEC255-22-2, Class III Electromagnetic field test (Radiated electr. magn. field test) IEC255-22-3, Class III Fast transient test IEC41B(CO)53, Class III	2.5 kV (peak); 1 MHz $\tau = 15 \mu\text{s}$; duration 2 s 8 kV (peak); 5 ns/30 ns; 10 positive discharges frequency 27 MHz to 500 MHz; 10 V/m 2 kV (peak); 5/50 ns; 5 kHz; 4 mJ per impulse
Radio interference	DIN VDE 0871, limit class B	
Climatic conditions	Permissible ambient temperature according to IEC 255 and IEC 870 in service during storage during transport Humidity rating	-5° to +55 °C -25° to +55 °C -25° to +70 °C Annual average ≤ 75% relative humidity on 30 days/year up to 95% relative humidity; condensation not permissible
Mechanical stress tests	According to IEC 68 basic specification and IEC 255-21 in service during transport	10 Hz to 60 Hz: 0.035 mm amplitude 60 Hz to 500 Hz: 0.5 g acceleration 5 Hz to 8 Hz: 7.5 mm amplitude 8 Hz to 500 Hz: 2 g acceleration

7SV512 numerical circuit-breaker failure protection relay

Technical data

Setting ranges	Circuit-breaker failure protection			
	Initiation conditions			With or without current, 1 or 3 pole
	Current detection	step	0.01 I_n	0.05 I_n to 4 I_n
	Reset ratio			0.9
	Delay times	all delay stages	0.01 s	0 to 32 s, or ∞ (off)
	Pick-up time			± 5 ms
	Reset time	sinusoidal current maximum		≤ 10 ms (typical 5 ms) ≤ 20 ms (typical 15 ms)
	Tolerances			
	Current pick-up value (0.1 I_n – 4 I_n)			± 5 % of set value
	Current pick-up value (0.05 I_n – 0.1 I_n)			± 10 % of set value
	Time			± 1 % or a minimum of 10 ms
End fault protection	Delay time	step	0.01 s	0 to 32 s, or ∞ (off)
	Tolerances	time		± 1 % or a minimum of 10 ms
Pole discrepancy protection	Start criterion			any one or two poles open
	Delay time	step	0.01 s	0 to 32 s, or ∞ (off)
	Tolerances	time		± 1 % or a minimum of 10 ms
Disturbance recording	Measured values			$I_{L1}, I_{L2}, I_{L3}, I_E$
	Trigger			Trip, or fault detection, or binary input
	Recording period (50 Hz)			–100 ms to max. 2900 ms
	Recording period (60 Hz)			–83 ms to max. 2417 ms
	Holding time			Until next fault
Additional functions	Values for operating/on-line measurements			
	Current			$I_{L1}, I_{L2}, I_{L3}, I_E$ (in primary amps or % of I_n)
	Effective range			10 % I_n to 240 % I_n
	Tolerance			<2 % of respective rated value

Selection and ordering data

7SV512 numerical circuit-breaker failure protection relay	Order No. 7SV512 □ - □ □ A 0 □ - 0 □ A 0
Rated current at 50/60 Hz AC 1 A 5 A	↑ 1 5
Rated auxiliary voltage 24, 48 V DC 60, 110, 125 V DC 220, 250 V DC	↑ 2 4 5
Construction for panel surface mounting for flush mounting or cubicle mounting	↑ B C
Real-time clock and non-volatile annunciation memory without with	↑ 0 1
Serial interface without interface with integrated fibre optic serial interface (820 nm)	↑ A C

Devices for Various Applications

7SV512 numerical circuit-breaker failure protection relay




Fig. 2
Diagram showing the trip release function

7SV512 numerical circuit-breaker failure protection relay




Fig. 3 Connection diagram for the 7SV512 numerical circuit-breaker failure protection relay

Devices for Various Applications

Dimension drawings in mm




Fig. 4
7SV512 with housing 7XP2030-2 (for panel flush mounting or cubicle mounting)




Fig. 5
7SV512 with housing 7XP2030-1 (for panel surface mounting with two-tier terminals)

Conditions of Sale and Delivery • Export Regulations • Trademarks • Dimensions

Conditions of Sale and Delivery

Subject to the General Conditions of Supply and Delivery for Products and Services of the Electrical and Electronic Industry and to any other conditions agreed upon with the recipients of catalogs.

■ The technical data, dimensions and weights are subject to change unless otherwise stated on the individual pages of this catalog.

The illustrations are for reference only.

We reserve the right to adjust the prices and shall charge the price applying on the date of delivery.

A 9.91 a

Export Regulations

In accordance with present German and US export regulations export licences (dated 02.95) are not required for the products listed in this catalog. Export and re-export are therefore

permissible without the approval of the relevant authorities except where current German export regulations contain country-specific restrictions.

Subject to change. Relevant are the criteria stated in the delivery note and in the invoice. An export licence may be required due to country-specific application of the product.

Trademarks

All product designations used are trademarks or product names of Siemens AG or of suppliers.

Dimensions

All dimensions in this catalog are given in mm

Responsible for

Technical contents: Norbert Schuster,
Siemens AG, EV S T11, Nürnberg

General editing: Claudia Kühn-Sutiono,
Siemens AG, EV MK 2, Erlangen

Bereich
Energieübertragung und -verteilung
Geschäftsgebiet
Zähler, Sekundär- und Netzleittechnik
P. O. Box 48 06
D-90026 Nürnberg



Power
Transmission
and Distribution