



**SIEMENS**

*Ingenuity for life*

# SIERS integrated electrical racking system family

## For medium-voltage air-insulated switchgear, medium-voltage motor controllers, and low-voltage motor control centers

Siemens integrated electrical racking system (SIERS) provides additional personnel protection against arc-flash exposure for operators by providing a means of remotely racking GM-SG non-arc-resistant, GM-SG-AR arc-resistant, and GM38 medium-voltage air-insulated switchgear, SIMOVAC™ non-arc-resistant and SIMOVAC-AR™ arc-resistant medium-voltage controllers, or tiastar™ low-voltage motor control centers.

SIERS delivers a safe, easy-to-use, cost-effective, reliable and flexible way to remotely operate equipment while standing outside of the arc zone and reduces the need for personal protective equipment (PPE) per the NFPA-70E® standard.

### Safety features:

- Maintains all of the safety interlocks as required by IEEE Std. C37.20.2, UL 347, and UL 845

- If interference is experienced while racking, the retractable stabs, circuit breaker, or auxiliary tray will attempt to return to the DISCONNECTED position or the non-load isolation switch will attempt to return to the OFF position

- The control pendant (hand-held controller) provides clear light-emitting diode indication of the position of the non-load isolation switch, retractable stabs, circuit breaker, or auxiliary tray.

- When plugged into a specific compartment, the control pendant will override any electronic control system (HMI, SCADA or similar).

### Easy to use and operate:

- User-friendly control pendant with easy to read display and controls

- Provisions for energizing SIERS with an external 120 Vac power supply with an extension cord (optional)
- The high-torque, fixed-mounted motor integrated in the compartment provides smooth and efficient movement of the non-load isolation switch, retractable stabs, circuit breaker, or auxiliary tray between positions.

### Reliable:

- Logic to sense interference issues during operations
- Operation is smooth and consistent
- Control pendant is industrial class
- Factory installed and tested as an integrated system.

### Flexible:

- Powered from a control power transformer located in the assembly at 120 Vac, or by an external supply (either 120 Vac or 125 Vdc)
- Controls can be integrated into the secondary control circuits interface with the protection relay to provide interface with SCADA systems, local HMI or discrete wiring
- Available as a field retrofit for existing Siemens equipment.

### Control options:

- SIERS devices are available in three control configurations: basic version, local HMI version (Sm@rtGear™ technology), and custom version, e.g., SCADA or other systems.

Features	Available with Siemens products					
	GM-SG	GM-SG-AR	GM38	SIMOVAC	SIMOVAC-AR	tiastar
Remote circuit breaker racking	X	X	X			
Remote isolation switch operator				X	X	
Remote retractable stabs operator						X
Remote closed door racking	X	X	X	X	X	X
Fixed-integrated motor	X	X	X	X	X	
Portable motor						X
Hand-held controller (pendant)	X	X	X	X	X	X
Local HMI interface	X	X	X	X	X	
Remote SCADA interface	X	X	X	X	X	

Type	Configuration	Description
Basic	1	<p>Each circuit breaker, auxiliary tray, or controller cell is equipped with a SIERS integrated electrical racking system, which includes a high-torque, fixed-mounted motor, logic-control module, control-pendant connector powered by control power in the equipment or an external supply (either 120 Vac or 125 Vdc) when necessary. Typically, one control pendant is supplied per lineup.</p> <ul style="list-style-type: none"> <li>SIERS integrated electrical racking system; one per circuit breaker, auxiliary tray, or main contactor cell plus one control pendant per lineup.</li> <li>Each tiastar unit with SIERS includes the retractable stab mechanism and can optionally include a remote operator mechanism with control pendant. It is recommended one remote operator be purchased per installation (sold separately).</li> </ul>
Local HMI	2	<p>Basic type plus local HMI panel PC interface with SIMOVAC, SIMOVAC-AR, GM-SG, GM-SG-AR or GM38 lineup(s) in the electrical room: a control power transformer located in the assembly at 120 Vac, or by an external supply (either 120 Vac or 125 Vdc)</p> <ul style="list-style-type: none"> <li>Panel PC display HMI with easy-to-use graphic interface.</li> </ul>
Remote SCADA	3	<p>Basic type plus custom interface with SCADA or other system:</p> <ul style="list-style-type: none"> <li>Local HMI (optional).</li> </ul>



SIERS for medium-voltage switchgear



SIERS for medium-voltage motor controllers



SIERS for low-voltage motor control centers

Published by Siemens Industry, Inc. 2018.

Siemens Industry  
7000 Siemens Road  
Wendell, North Carolina 27591

For more information, including service or parts,  
please contact our Customer Support Center.  
Phone: 1-800-333-7421

[www.usa.siemens.com/mediumvoltage](http://www.usa.siemens.com/mediumvoltage)

Article No. EMMS-T40109-00-4AUS

Printed in U.S.A.

© 2018 Siemens Industry, Inc.

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.